

PST-360

Hall-Effect Through-Shaft Rotary Position Sensor



Available with




•PATENTED•

KEY FEATURES




True non-contact operation

With no gears or mechanical interfaces, the sensor is easy to assemble and calibrate and exhibits minimal wear over its service life.



Through-hole design

Allows shaft insertion from the top or bottom and simplifies assembly in space-constrained applications.




360-degree absolute position feedback

Continuous mechanical rotation without dead-band; retains position through power loss. Programmable electrical angles from 15° to 360°.



Made for harsh environments

The rugged package protects the sensor from dust, moisture, vibration and extreme temperatures for usage in the most demanding environments.



Durable and robust design

The non-contacting design allows for an extra-long product lifetime of up to 50 million cycles.



Configurable

Programmable transfer function and switch outputs; multiple output protocols and redundancy options.

The PST-360 is a Hall-effect through-shaft rotary position sensor that provides accurate absolute angle feedback using a true noncontact sensing element.

Mounted directly at the pivot point, it requires no levers, connecting rods, or other mechanical interfaces.

The design tolerates shaft eccentricity, mounting tolerances, and mechanical wear over the application's life. The device offers endless rotation with a programmable angular range (15° to 360°), multiple output options, and support for both low- and high-voltage supplies. Multi-turn configurations are available upon request.

POTENTIAL APPLICATIONS

Industrial

- ▶ Autonomous warehouse robotics
- ▶ Robotics and automation feedback
- ▶ Robot arm position
- ▶ Valve monitoring
- ▶ Conveyor operation

Transportation

- ▶ Steering angle
- ▶ Pedal position
- ▶ Fork height and mast tilt
- ▶ Bucket position
- ▶ Hitch position
- ▶ Boom angle
- ▶ Joystick controls

Marine

- ▶ Steering and shifter sensor
- ▶ Engine throttle

Home and Building Automation

- ▶ HVAC systems

Medical




- ▶ Electric hospital bed
- ▶ Mobility chair steering and throttle

PST-360

Hall-Effect Through-Shaft Rotary Position Sensor


DIMENSIONS (MM)

Outer Dimensions




Download the STEP files at:
www.piher.net

The shaft should be made of non-ferromagnetic material. If a ferromagnetic shaft is required, please contact Piher.




Sensor shown above is the 17mm version with the rotor at zero position. The sensor is delivered in a random position. Wires: 0.35mm² TXL SAE J1128



14mm rotor



17mm rotor



Recommended shaft dimensions



WIRING/CONNECTION DIAGRAM

Color	Simple		Redundant		Full-redundant Analog or PWM	CAN	SPI
	5V	7V to 15V	5V	7V to 15V			
Brown	Power supply	Power supply	Power supply	Power supply	Power supply 1	Power supply	Power supply
Blue	Ground	Ground	Ground	Ground	Ground 1	Ground	Ground
Black	Signal output	Signal output	Signal output 1	Signal output 1	Ground 2	CAN High	MOSI
White	n/a	n/a	Signal output 2	Signal output 2	Signal output 2	CAN Low	/SS
Red	n/a	n/a	n/a	n/a	Power supply 2	n/a	n/a
Yellow	n/a	n/a	n/a	n/a	Signal output 1	n/a	n/a
Grey	n/a	Not used	n/a	Not used	n/a	n/a	SCLK

Further instructions are available at www.piher.net. Connector assembly available on request.

PST-360

Hall-Effect Through-Shaft Rotary Position Sensor

HOW TO ORDER (Example: PST360G2-1A-C0001-ERA190-05K)

Simple Output - Analog, PWM or CAN

PST360G2	-	-	1	-	C ____	-	ERA ____	-	-	K	-	----
Series	Rotor ¹	Type	Output ²	Output function ³	Electric rotational angle ⁴	Voltage supply ⁵	Temp. range ⁶	PWM Frequency Hz ⁷				
	[empty] = 14mm B = 17mm	1 = simple	A = Analog P = PWM J = CAN SAE J1939 O = CANopen	C0000 C0001	ERA040 ... ERA360	05 = 5V ±10% RE = 7V-15V	Analog, PWM = -40°C to +125°C CAN: -40°C to +85°C	[empty] = 200Hz F100 = 100Hz F101 = 101Hz ... F999 = 999Hz				

Simple output - SPI

PST360G2	-	-	1	S	-	C_____	-	ERA____	-	__	K
Series	Rotor ¹	Type	Output ²	Output function ³	Electric rotational angle ⁴	Supply voltage ⁵	Temp. range				
	[empty] = 14mm B = 17mm	1 = simple	S = SPI	C0000 C0001	ERA040 ... ERA360	05 = 5V ±10% RE = 7V-15V	K = -40°C to +125°C				

Redundant output - Analog, PWM or CAN

PST360G2	-	—	2	—	-	C — — —	-	ERA — —	-	—	K	-	— — — —	— — — —
Series	Rotor ¹	Type	Output ²	Output function ³	Electrical rotational angle ⁴	Supply voltage ⁵	Temp. range ⁶	PWM Frequency Hz. [1] ⁷	PWM Frequency Hz. [2] ⁷					
	[empty] = 14mm B = 17mm	2 = redundant	AA = Analog PP = PWM JJ = CAN SAE J1939 OO = CANopen	C0002	ERA040 ... ERA360	05 = 5V ±10% RE = 7V-15V	Analogic, PWM = -40°C to +125°C CAN: -40°C to +85°C	F100 F101 ... F999	F100 F101 ... F999					

Full-redundant output - Analog or PWM

PST360G2	-	-	3	-	C	-	ERA	-	05	K	-	-	-
Series	Rotor ¹	Type	Output ²	Output function ³	Electrical rotational angle ⁴	Supply voltage	Temp. range	PWM Frequency Hz. (1) ⁷	PWM Frequency Hz. (2) ⁷				
	[empty] = 14mm B = 17mm	3 = full-redundant	AA = Analog PP = PWM	C0002	ERA040 ... ERA360	05 = 5V ±10%	-40°C to +125°C	F100 F101 ... F999	F100 F101 ... F999				

Full-redundant output - Analog and SPI

PST360G2	-	—	3	SSA	-	C ____	-	ERA ____	-	05	K
Series	Rotor ¹	Type	Output ⁸	Output function ⁸	Electrical rotational angle ⁸	Supply voltage	Temp. range				
	[empty] = 14mm B = 17mm	3 = full-redundant	SSA = Analog and SPI	CXXXX	ERA050 ERA090	05 = 5V ±10%	-40°C to +125°C				

1 Other rotors available on request.

2 The analog output is ratiometric, proportional: for supply voltage "5V" to input voltage; for supply voltage "RE" to 5V.

3 Other output functions available, please check availability. Enter CXXXX as long as the new output function is not defined.

4 Models with ERA < 40° available on request.

5 CAN models are available in 7V-15V. For other voltages up to 25V: check availability.

6 CAN models: other temperatures to be studied on request.

7 Leave blank if not applicable. Default frequency is 200 Hz.

8 Sensor with three isolated outputs, two SPI (tapers A and B) plus one Analog (taper C). All of them measure the same ERA. Check part numbering and specifications with Piher.





check inventory

PST-360

Hall-Effect Through-Shaft Rotary Position Sensor

SPECIAL ROTORS

Ref. 3457	Ref. 3458
	

For more information visit: www.piher.net

MOUNTING INSTRUCTIONS

1. Place the component on a flat surface.
2. Insert the application shaft (see recommended shaft dimensions) through the sensor's rotor, avoiding any mechanical play/wobble.
3. Fasten the two M5 screws (M5 washers are recommended).

OUR ADVANTAGE

- ▶ Leading-edge, innovative position-sensing solutions
 - ▷ Contactless (Hall-effect and Inductive Technology)
 - ▷ Contacting (Potentiometers, Printed Electronics)
- ▶ Engineering design-in support
- ▶ All our products can be customized to fit the target application and customer requirements
- ▶ Capability to move seamlessly from development to true high-volume production
- ▶ A global footprint with global engineering and commercial support
- ▶ One-stop shop not limited to position sensors (temperature, pressure, gas,...) through group collaboration
- ▶ Flexibility and entrepreneurship of a medium-sized company with the backing of Amphenol Corporation



To ensure you have the most up-to-date information, we recommend always downloading the latest version of this datasheet from www.piher.net

Disclaimer:

The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information. Piher Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Piher"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein. Piher disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which apply to these products. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher. The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Piher products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Piher for any damages arising or resulting from such use or sale. Please contact authorized Piher personnel to obtain written terms and conditions regarding products designed for such applications. Product names and markings noted herein may be trademarks of their respective owners. Information contained in and/or attached to this catalog may be subject to export control regulations of the European Community, USA, or other countries. Each recipient of this document is responsible to ensure that usage and/or transfer of any information contained in this document complies with all relevant export control regulations. If you are in any doubt about the export control restrictions that apply to this information, please contact the sender immediately. For any Piher Exports, Note: All products / technologies are EAR99 Classified commodities. Exports from the United States are in accordance with the Export Administration Regulations. Diversion contrary to US law is prohibited.

CONTACT

Piher Sensing Systems
 Polígono Industrial Municipal
 Vial T2, N°22
 31500 Tudela, Spain
sales@piher.net

+34 948 820 450



NEED QUICK HELP?

Our AI Virtual Assistant is available 24/7 to provide instant support—visit chat.piher.info now!

Rev: 14112025 © 2024 Piher Sensors & Controls S.A.