




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**

Strain Relief: **Without**

Primary Product Color: **Black**

Primary Product Material: **PBT GF20**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
---	-------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF20

Mechanical Attachment

Strain Relief	Without
---------------	---------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	288
Packaging Method	Bag

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)



Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1393450-5
V23542C1052B300=KABELBAUMST 80

Customers Also Bought

TE Part #CH02064001
VERSAFLEX-1-1/4-0-SP

TE Part #10142032-02
TRICAN 5V HTD2800P1B11C6 500kbps

TE Part #6-683454-5
CRIMPER, INSULATION, "O"

TE Part #2119582-2
Crimper, Insulation F Premium







TE Part #1393450-5
V23542C1052B300=KABELBAUMST 80




TE Part #1393436-4
V23542C1028B300=KABELBAUMST. 8



TE Part #1411594-1
ELOP2,8 F6000Y 65



TE Part #1393457-4
V23540M1000Z110=DICHTTULLE (F1



TE Part #140712-2
PIN .155 DIA REC 18-14 AWG TPBR



TE Part #60007-2
RING TERMINAL CRIMP TAB 26-22 AWG TPBR

Documents

Product Drawings

V23542C1052Z300=ABDECKK 52PDIC

English

CAD Files

Customer View Model

ENG_CVM_CVM_1393454-9_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1393454-9_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1393454-9_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.