





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/9/12	
A		UPDATE DIM.& SPEC.	9/26/18	AY/SL
B		UPDATE DIM.& SPEC.	3/17/20	OW/IW



RECOMMENDED PCB LAYOUT

POSITIONS	Dimension	
	A	B
2	.118 [3.00]	.380 [9.65]
3	.236 [6.00]	.498 [12.65]
4	.354 [9.00]	.616 [15.65]
5	.472 [12.00]	.734 [18.65]
6	.591 [15.00]	.852 [21.65]
7	.709 [18.00]	.970 [24.65]
8	.827 [21.00]	1.089 [27.65]
9	.945 [24.00]	1.207 [30.65]
10	1.063 [27.00]	1.325 [33.65]
11	1.181 [30.00]	1.443 [36.65]
12	1.299 [33.00]	1.561 [39.65]

SPECIFICATIONS:

Material:
 Insulator: LCP, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass

Plating:
 Tin over Copper underplate overall

Electrical:
 Voltage rating: 250 V
 Current rating: 5 Amps max.
 Contact resistance: 10 mohms max.
 Dielectric withstanding voltage: 1500 VAC for 1 minute

Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010		ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS		TITLE		
DATE		.118" [3.00MM] PITCH, PCB MOUNT HOUSING & TERMINAL RIGHT ANGLE, BOARD LOCKS		
DRAWN	AY			5/9/12
CHECKED	OC			5/9/12
APPROVED				
SIZE	PART NO.	REV.		
X	DML-1-XX-A-H-T-A-BL	B		
REF:	S00123T	SCALE:	NTS	
		SHEET 1 OF 1		