








Technical data

- Nominal voltage: 300V/8A
PITCH:3.5mm
- Insulation Withstanding Voltage:
AC1600V/MIN
- Insulation Resistance:
1000MΩ or more at DC500V
- Operating temperature range:-40°C ~115°C
- Soldering temperature range:250°C±10°C/5sec
- Safety approval:
- RoHS Compliance
- Undimensioned Tolerances:

Dim.L=(P-1)x3.5+4.9 Dim.B=(P-1)x3.5 P= number of poles		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

Part No.:

OSTOQXX1251

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

COLOR
0: Black
2: Red
3: Orange
4: Yellow
5: Green (Standard)
6: Blue
8: Grey

Nonstandard colors
Mins could apply

2	PIN	BRASS	TIN PLATED	P
1	BODY	PA66 UL94V-0		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
DWG	WF. Zhang	DATE 2016.03.31	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2016.05.21	SCALE: NONE 4:1 (:) REV: A	Tolerance
APP.		DATE	TITLE: OSTOQ 3.50 Series	X. ±0.50
			Close type Right-angle(90D)	X.X ±0.30
			PART NO. OSTOQXX1251	X* ±1.0
			DWG NO. OSTOQXX1251.dwg	±1°

SIGN	DESCRIPTION	CHK.	DATE



ON-SHORE TECHNOLOGY, INC.