

DIN-Signal high current f, 40A press-in



Image is for illustration purposes only. Please refer to product description.

Part number	09 03 000 6250
Specification	DIN-Signal high current f, 40A press-in
HARTING eCatalogue	https://b2b.harting.com/09030006250

Identification

Category	Contacts
Series	DIN 41612
Type of contact	Press-in contact
Description of the contact	Straight
Contacts for	DIN 41612 Type M-flat

Version

Gender	Female contact for female connectors
Manufacturing process	Turned contacts

Technical characteristics

Operating current	≤40 A
Performance level	1
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No



Pushing Performance

Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	DIN 41626
----------------	-----------

Commercial data

Packaging size	100
Net weight	0.01 g
Country of origin	Czechia
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.
Measuring and testing techniques acc. to IEC 60512-5-2

