


Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant



Product Highlights:

- ? 3SBC 1/5 - Size Relay Series
- ? Input Voltage = 12 VDC
- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Contact Current Rating = 2 Amps.
- ? Non Polarized, Monostable Coil
- ? Magnetic System

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Termination Type = PC Pins

Electrical Characteristics:

- ? Input Voltage (VDC) = 12
- ? Contact Current Rating (Amps.) = 2
- ? Coil Polarity Protection Diode = Without
- ? Transistor Driver = Without
- ? Coil Resistance (?) = 210
- ? MOSFET Driver = Without
- ? Coil Power Measurement = Milliwatts
- ? Coil Power, Nominal (mW) = 686
- ? Actuating System = DC
- ? Shock = 75 G's, 6ms
- ? Vibration = 30G's, 10 to 3000Hz

Body Related Features:

- ? Series = 3SBC 1/5 - Size Relay

Contact Related Features:

- ? Mounting Options = PC Board
- ? Enclosure = Hermetically Sealed
- ? Approved Standards = M39016 Qualified, Level

Configuration Related Features:

- ? Contact Arrangement = 2 Form C, DPDT, 2 C/O
- ? Coil Magnetic System = Non Polarized, Monostable
- ? Coil Suppression Diode = Without

Industry Standards:

- ? Government/Industry Qualification = Yes
- ? Government/Industry Part Number = M39016/13 -056L
- ? RoHS/ELV Compliance = Not ELV/RoHS compliant
- ? Lead Free Solder Processes = Not suitable for lead free processing

Conditions for Usage:

- ? Temperature Range (°C) = -65 – +125

Other:

- ? Brand = CII