


PART NUMBER  
SSB-LX2450YW



REV.  
C

REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	E.C.N. #10113.	7.26.96
B	E.C.N. #10BRDR. & REDRAWN.	6.21.01
C	ECN-Lumex201600057	09.01.16



ELECTRO-OPTICAL CHARACTERISTICS  $T_A=25^\circ\text{C}$


PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		585		nm	
FORWARD VOLTAGE		2.1	2.6	$V_f$	
REVERSE VOLTAGE			5.0	$V_r$	$I_r=100\mu\text{A}$
LUMINOUS INTENSITY		38		mcd	$I_f=20\text{MA}$
EMITTED COLOR: YELLOW					
EPOXY LENS FINISH: YELLOW DIFFUSED					



LIMITS OF SAFE OPERATION AT  $25^\circ\text{C}$  PERDIE

PARAMETER	MAX	UNITS
FORWARD CURRENT	20	mA
OPERATING, STORAGE TEMP.	-40 TO +85	$^\circ\text{C}$
SOLDERING TEMP.**	MAX. 3SEC.@260	$^\circ\text{C}$

\*\*2mm BELOW PACKAGE BASE



\*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION -0.00 MAX= +0.00 -DECIMAL PRECISION

REV.	PART NUMBER
C	SSB-LX2450YW

5mm x 20mm 4 CHIP LIGHT BAR,  
585nm YELLOW CHIPS, MILKY WHITE DIFFUSED.

**CONFIDENTIAL INFORMATION**  
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

**RELIABILITY NOTE**  
OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

**LUMEX**  
Creating LED and LCD Solutions Together™  
425 N. GARY AVE.  
CAROL STREAM, IL 60188  
PHONE: 800-278-5666  
FAX: 630-315-2152  
WEB: WWW.LUMEX.COM

DRAWN BY:	CHECKED BY:	APPROVED BY:	DATE:
K.Y.	G.Y.	R.C.	09.01.16
			PAGE: 1 OF 1
			SCALE: N/A