



Part Number : [1200868052](#)
Product Description : Nano-Change (M8)
Single-Ended Cordset with Knurled Hexnut, 3
Poles, A-Coded, Female (90°) to Pigtail,
0.25mm² Black PUR LSOH Cable, 2.0m (6.56')
Length
Series Number : 120086
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : 403001H08M020




Documents & Resources

Drawings
[1200868052_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 3 Poles, A-Coded, Female (90°) to Pigtail, 0.25mm ² Black PUR LSOH Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	883906389475

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	4.10mm (.161")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded

LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	54.000/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 21198
Wire Size (AWG)	24

This document was generated on Apr 19, 2025