



**Part Number :** [1053072206](#)

**Product Description :** Nano-Fit Receptacle Housing,  
TPA Capable, 2.50mm Pitch, Single Row, 6 Circuits,  
Natural, Glow-Wire Capable

**Series Number :** 105307

**Status :** Active

**Product Category :** Connector Housings



---

## Documents & Resources

### Drawings

[1053072206\\_sd.pdf](#)

[PK-105307-100-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-105300-100-001.pdf](#)

[1053001000-PS-CH-000.pdf](#)

[1053001000-PS-ES-000.pdf](#)

[1053001000-PS-JP-000.pdf](#)

[1053001000-PS-SK-000.pdf](#)

[PS-105300-100-001.pdf](#)


[1053000000-TS-000.pdf](#)

[1053001000-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant

Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Active
Category	Connector Housings
Series	105307
Description	Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Single Row, 6 Circuits, Natural, Glow-Wire Capable
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Nano-Fit
UPC	889056026635

**Agency**

CSA	LR19980
UL	E29179

**Physical**

Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.670/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Kinked Pins, Tin (Sn) Plating, Natural, Glow-Wire Capable, Tray	<a href="#"><u>1053092106</u></a>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Kinked Pins, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	<a href="#"><u>1053092206</u></a>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Kinked Pins, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	<a href="#"><u>1053092306</u></a>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6	<a href="#"><u>1053092406</u></a>

Circuits, with Kinked Pins, 0.76µm Gold (Au) Plating, Lubricated, Natural, Glow-Wire Capable, Tray	
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Solder Clips, Tin (Sn) Plating, Natural, Glow-Wire Capable, Tray	<u>1053112106</u>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Solder Clips, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	<u>1053112206</u>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Solder Clips, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	<u>1053112306</u>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, with Solder Clips, 0.76µm Gold (Au) Plating, Lubricated, Natural, Glow-Wire Capable, Tray	<u>1053112406</u>
Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Tin (Sn) Plating, Natural, Glow-Wire Capable	<u>1054312106</u>
Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable	<u>1054312206</u>
Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable	<u>1054312306</u>
Nano-Fit Vertical Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, Lubricated, Natural, Glow-Wire Capable	<u>1054312406</u>
Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, Tin (Sn) Plating,	<u>1053132106</u>

Natural, Glow-Wire Capable, Tray	
Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	<u>1053132206</u>
Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	<u>1053132306</u>
Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, Lubricated, Natural, Glow-Wire Capable, Tray	<u>1053132406</u>
Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Tin (Sn) Plating, Natural, Glow-Wire Capable	<u>1054302106</u>
Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable	<u>1054302206</u>
Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable	<u>1054302306</u>
Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Single Row, 6 Circuits, 0.76µm Gold (Au) Plating, Lubricated, Natural, Glow-Wire Capable	<u>1054302406</u>
Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Single Row, 6 Circuits, Natural, Glow-Wire Capable	<u>2002772106</u>
Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Single Row, 6 Circuits, Natural, Panel Mount,	<u>2002772206</u>

Glow-Wire Capable	
-------------------	--

## Use with Part(s)

Description	Part Number
Nano-Fit Connector Position Assurance (CPA) Retainer, UL 94V-0, Red	<u>2171401000</u>
Pre-Crimped Lead Nano-Fit Female-to-Nano-Fit Female, Gold (Au) Plating, 150.00mm Length, 20 AWG, Black	<u>797582129</u>
Pre-Crimped Lead Nano-Fit Female-to-Nano-Fit Female, Gold (Au) Plating, 300.00mm Length, 20 AWG, Black	<u>797582130</u>
Pre-Crimped Lead Nano-Fit Female-to-Nano-Fit Female, Matte Tin (Sn) Plating, 150.00mm Length, 20 AWG, Black	<u>797582139</u>
Pre-Crimped Lead Nano-Fit Female-to-Nano-Fit Female, Matte Tin (Sn) Plating, 300.00mm Length, 20 AWG, Black	<u>797582140</u>
Nano-Fit Female Crimp Terminals	<u>105300</u>
Nano-Fit Terminal Position Assurance (TPA) Retainers	<u>105325</u>

## Application Tooling

### Global

Description	Part Number
Extraction Tool for Nano-Fit Power Connectors and Crimp Terminals, 26-20 AWG	<u>638244600</u>

This document was generated on Sep 11, 2025