



By Burndy
Catalog # [BIT2/O](#)

Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 1 Sided Entry, 14-2/O AWG, Al/Cu Rated



Features

- Type BIT and BITO (Offset) Multi-tap connectors are installed quickly and easily
- Suitable for use on Code conductor
- UL486B Listed, Dual-rated AL9CU.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

EU RoHS Indicator	Yes
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - UL Listed Direct Burial	No
Buy American Compliant	Yes
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024);BABA Compliant (All status valid till December 2024)

Conductor

Conductor - Copper Str Size Range	14 AWG - 2/O AWG
Conductor Type	AL C Str-Size;CU C Str-Size
Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/O AWG;2/O AWG
Conductor - AL Str Size Range	14 AWG - 2/O AWG

Configuration

Physical Attribute - Number of Screws	2
Number Of Ports	2

Current

Voltage - Maximum	600 V
Operating Voltage	600 V

Dimensions

Dimension - Width inch	1.4 in
Dimension - Width mm	36 mm
Dimension - Height fraction	1.375 in
Dimension - Height inch	1.38 in
Dimension - Height mm	35 mm
Dimension - Width fraction	1-2/5 in

Force Related

Installation Torque	120 in-lb
Recommended in-lb	

General

Sub Brand	UNITAP
Material - Hardware	Aluminum
Physical Attribute - Screw Type	Allen
Insulation Type	Plastisol
Trade Name	UNITAP™
Type	BIT
UPC 12 Digit	781810134061
UPC 14 Digit GTIN	00781810134061
Material	Aluminum
Hex Key	3/16 in
UPC	781810134061

Logistics

Carton Quantity	250
Minimum Pack Quantity	1

Operational

Temperature Rating	90 °C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)