

Capacitor > Ceramic Capacitor (Capacitor) > Ceramic Capacitor (SMD)

Automotive Chip Multilayer Ceramic Capacitors

Please be sure to read this before using the product.
Precautions regarding counterfeit products

GCM155R11C104KA40 # The "x" is the packaging code.


生産中



<List of product numbers with packaging code>

GCM155R11C104KA40D GCM155R11C104KA40J GCM155R11C104KA40W

Appearance and shape



spec

Search for products with similar specifications

L dimension	1.0 ± 0.05mm
W dimension	0.5 ± 0.05mm
T dimension	0.5 ± 0.05mm
Capacitance	0.10μF ± 10%
Distance between external electrodes g	0.3mm min.
External electrode dimensions e	0.15 to 0.35 mm
Operating temperature limit	-55 °C ~ 125 °C
Rated voltage	16Vdc
Size code mm	1005M
Capacitance change rate	± 15.0%
Temperature characteristics (compliant standard)	R (JIS)
Temperature range of temperature characteristics	-55 °C ~ 125 °C

Product Search Assistant We propose candidate products of the same size or smaller size with similar specifications.







- ☒ Small size ☒ High capacity ☒ High withstand voltage
- ☒ High temperature support ☒ Emphasis on DC bias characteristics
- ☒ Find a silicon capacitor with a similar capacity

Reference information

Packaging code	specification	Standard packing quantity
D	180mm paper taping	10000
J	330mm paper taping	50000
W	180mm paper tape (W8P1)	20000

Mass (typical value)	
1 piece	1.5mg
φ 180mm reel	118g

Characteristic data



(Simulating) More detailed graph

Product inquiries

Sample inquiry

Inquiry for quotation

Technical inquiry

20pcs free sample

Agency / Web trading company (Inventory search)

Download this page as PDF

How to read the product number

Series details

Detailed information

Detailed spec sheet
-Rated value
-Performance and test method
-Packaging method
-Caution / Precautions for use (storage / mounting / land dimension s / cleaning / transportation, etc.)

Product data

SPICE Netlist (mod format)

Sparameter (S2P format)

Structural drawing

Reliability test data * Representative data

Related information

Proposal of new packaging

SnapEDA

CAD Models

Share this page



Contact Us

Official SNS

Product Information

[Electronic components](#)
[solution](#)
[Completed equipment / others](#)

application

support

[FAQ](#)
[PDF download](#)
[Video library](#)
[Main base information](#)
[Inventory search](#)

Product news

Technical article

my Murata

Event

Webinar

Special feature



European RoHS /
REACH compatible
Compatible with
California Proposition
65

We will explain the regulatory
laws and regulations
regarding chemical
substances contained in
products and our response to
them.

公益財団法人
村田学術振興財団

