


* UNLESS OTHERWISE SPECIFIED TOLERANCES ON DECIMAL IS:

DIMENSIONS(mm/in)				
SIZE	A $\pm\frac{.50}{\pm0.02}$	B $\pm\frac{.50}{\pm0.02}$	C $\pm\frac{.50}{\pm0.02}$	D $\pm\frac{.25}{\pm0.01}$
9	31.20	39.90	15.00	24.99
	1.228	1.571	0.591	0.984
15	39.50	41.50	15.00	33.32
	1.555	1.634	0.591	1.312
25	53.40	48.60	15.00	47.04
	2.102	1.913	0.591	1.852
37	69.70	53.60	15.00	63.50
	2.744	2.110	0.591	2.500

MATERIAL: DIE-CAST ZINC ALLOY
PLATING: NICKEL
JACKSCREWS: STEEL, ZINC PLATED
M3 HOODSCREWS: STEEL, ZINC PLATED
COMPRESSION INSERT: ABS UL 94-HB
COMPRESSION SPRING: STEEL, NICKEL PLATED
OPERATING TEMP: -40°C TO +120°C

BACKSHELL KIT INCLUDES:

- (2)BACKSHELL HALVES
- (2)4-40 THUMBSCREWS
- (2)HOUSING SCREWS
- (1)SET OF COMPRESSION INSERTS-VARIOUS SIZES
DIAMETERS:4mm(.157"),5mm(.197"),7mm(.276"),9mm(.351")

**NOTE: 3 in-lbs IS RECOMMEND TORQUE FOR HOUSING SCREWS

970-YYY-030R121

SERIES _____
POSITIONS _____
009
015
025
037
MATERIAL _____
030 = ZINC ALLOY
COLOR _____
12 = NICKEL OVER COPPER
PUT-UPS _____
1 = KIT

UNITS = "as specified" DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:
06/10/2005

NorComp



SCALE:
NTS

SHEET OF
1 2

REV
16

DWG NO.

970-YYY-030R121



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS
DATE:
06/10/2005

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
2 2

REV
16

DWG NO.

970-YYY-030R121