




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL RELEASE	FEB6,2023	K.T



TYPICAL FOR SINGLE COLOR



TYPICAL FOR BI-COLOR
(E.G. BIC GREEN/YELLOW)



EXAMPLE:
PART NUMBER: RJE36-188-3XXC-H

LED COLOR CODE

CODE	LED 2(LEFT)	LED 1(RIGHT)	CODE	LED 2(LEFT)	LED 1(RIGHT)	CODE	LED 2(LEFT)	LED 1(RIGHT)
0	BLOCKED	BLOCKED	9	GREEN	BLOCKED	J	BIC RD/GR	YELLOW
1	YELLOW	GREEN	A	BIC GR/YE	BIC GR/YE	K	YELLOW	BIC GR/OR
2	BLOCKED	GREEN	B	BIC RD/GR	BIC RD/GR	L	BIC GR/YE	RED
3	YELLOW	BLOCKED	C	BIC RD/GR	BIC GR/YE	M	RED	YELLOW
4	GREEN	YELLOW	D	GREEN	BIC GR/YE	N	BIC GR/RD	BIC GR/YE
5	GREEN	GREEN	E	YELLOW	BIC GR/YE	P	GREEN	BIC RD/GR
6	YELLOW	YELLOW	F	BIC GR/YE	YELLOW	R	BIC GR/OR	GREEN
7	RED	GREEN	G	BIC GR/OR	BIC GR/OR	T	RED	RED
8	GREEN	RED	H	BIC GR/YE	GREEN	V	BIC RD/GR	GREEN

PRIMARY COLOR FOR BI-COLOR
LEDS IN STANDARD ANODE/CATHODE
CONFIGURATION IS:
RED-GREEN=RED
RED-YELLOW=RED
GREEN-YELLOW=GREEN
GREEN-ORANGE=GREEN


LEGEND
BIC= BI-COLOR LED
YE=YELLOW
GR=GREEN
RD=RED
OR=ORANGE

NOTE:
THE TWO DIGITS PRECEDING THE
ADDITIONAL LED CODE MUST BE
USED IN THE PART NUMBER, WHEN
ORDERING ANY OF THE ADDITIONAL
LED OPTIONS.

UNLESS SPECIFIED OTHERWISE		DRAWN	KELVIN.T	FEB6,23	Amphenol Canada Corp. Commercial Products 8P8C MODULAR JACK OVER TWO TYPE C SHIELDED, WITH LED OPTIONS -RoHS COMPLIANT			
PRIMARY UNITS MILLIMETRES		CHECKED						
SECONDARY INCHES		M.E. APP'D						
REFERENCE IN PARENTHESES		Q.A. APP'D						
GENERAL TOLERANCES		DWG APPR.						
1 DECIMAL PLACE ±0.50		ENG. REL. NO.			DWG. NO.			REV A
2 DECIMAL PLACES ±0.35		REF.						
3 DECIMAL PLACES ±0.20		THIRD ANGLE PROJECTION  DO NOT SCALE DRAWING			P-RJE36-188-3XXC-H			
ANGULAR DEGREES ±1.5°					CODE ID NO. 03554			DWG SIZE: X

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	INITIAL RELEASE	FEB6,2023	K.T



PACKAGING NOTES:

- 1. ONE TRAY SHOULD HOLD 50PCS CONNECTORS.
- 2. A FULLY LOADED CARTON SHOULD CONTAIN 10 TRAYS(500PCS) OF CONNECTORS.

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE PRIMARY UNITS MILLIMETRES SECONDARY INCHES REFERENCE IN PARENTHESES GENERAL TOLERANCES 1 DECIMAL PLACE ± 0.50 2 DECIMAL PLACES ± 0.35 3 DECIMAL PLACES ± 0.20 ANGULAR DEGREES $\pm 1.5^{\circ}$	DRAWN	KELVIN.T	FEB6,23	Amphenol Canada Corp. Commercial Products 8P8C MODULAR JACK OVER TWO TYPE C SHIELDED, WITH LED OPTIONS -RoHS COMPLIANT			
	CHECKED						
	M.E. APP'D						
	Q.A. APP'D			DWG. NO. P-RJE36-188-3XXC-H REV A			
	DWG APPR.						
REF.	ENG. REL. NO.			CODE ID NO. 03554 DWG SIZE: X SCALE: 2:1 SHEET 3 OF 3			
THIRD ANGLE PROJECTION			DO NOT SCALE DRAWING				