

# C44P-R, 330 - 1,000 VAC/700 - 2,300 VDC, for PFC & AC Filter

## Overview

The C44P-R capacitor is a polypropylene metallized film capacitor with a cylindrical, aluminium can-type design filled with a soft, vegetable oil-based, polyurethane resin. It uses screw terminals, a plastic insulator, and an overpressure safety device.

## Applications

Typical applications include commutation, power factor correction, and AC harmonic filtering.

## Benefits

- Overpressure safety device
- High peak current capability
- High torque screw terminals with plastic insulator
- Long lifetime
- Self-healing




## Part Number System

| C                                     | 44                   | P             | L                                                                                                       | G              | R                     | 6                                                                                                                                     | 4                         | 0         | 0                 | R | AS | J |
|---------------------------------------|----------------------|---------------|---------------------------------------------------------------------------------------------------------|----------------|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------|---------------------------|-----------|-------------------|---|----|---|
| Series                                | Application          | Rated Voltage | Case Type                                                                                               | Terminal Style | Capacitance Code (pF) | Filling                                                                                                                               | Internal Codes            | Tolerance |                   |   |    |   |
| MKP Capacitors for Power Applications | 44 = 330 - 1,000 VAC | AC filter     | L = 330 VAC<br>K = 440 VAC<br>M = 480 VAC<br>P = 550 VAC<br>R = 640 VAC<br>U = 780 VAC<br>X = 1,000 VAC | G = M12 bolt   | R = Male M10          | Digits nine, ten, and eleven indicate the first three digits of capacitance value. Digit 8 indicates the number of zeros to be added. | Polyurethane resin filled |           | J = 5%<br>K = 10% |   |    |   |

*It is not possible to manufacture every part number which could be created from coding description. Please refer to table of standard part numbers and ask KEMET for other possibilities.*

**Built Into Tomorrow**

Dimensions – Millimeters



| Diameter                 | S  | W  | W1 | M1 | H1 |
|--------------------------|----|----|----|----|----|
| $\varnothing = 65$       | 28 | 18 | 40 | 12 | 16 |
| $\varnothing \geq 75$    | 35 | 21 | 45 | 12 | 16 |
| All dimensions are in mm |    |    |    |    |    |

| Maximum Driving Torque |          |
|------------------------|----------|
| Terminals M10          | 10 [N*m] |
| Bolt M12               | 12 [N*m] |

## General Technical Data

|                                                                       |                            |
|-----------------------------------------------------------------------|----------------------------|
| Reference Standards                                                   | IEC 61071                  |
|                                                                       | UL810 approved             |
| Dielectric                                                            | Polypropylene film         |
|                                                                       | Non-inductive type winding |
| Climatic Category                                                     | 25/70/56 – IEC 60068-1     |
| Maximum hot spot temperature                                          | +80°C                      |
| Endurance Test IEC 61071                                              | +70°C at case temperature  |
| Installation                                                          | Any position               |
| Tinned brass deck with self-extinguishing UL 94 V0 plastic insulators |                            |

## Electrical Characteristics

|                                                        |                                            |
|--------------------------------------------------------|--------------------------------------------|
| Rated Voltage                                          | $U_{rms}$ = (see table) VAC                |
| Surge Voltage                                          | $U_s$ = (see table) VDC                    |
| Capacitance Tolerance                                  | ±5% or ±10%                                |
| Dissipation Factor PP typical (tgδ0)                   | ≤ 0.0002 at 25°C                           |
| Storage Temperature                                    | -40 to 85°C                                |
| Relative Humidity                                      | Annual average ≤ 80% at 24°C               |
|                                                        | On 30 days/year permanently 100%.          |
|                                                        | On other days occasionally 90%.            |
|                                                        | Dewing not admitted                        |
| Capacitance deviation in temperature range (-40 +50°C) | ±1.5% maximum on capacitance value at 20°C |

## Life Expectancy

|                                 |                                                                |
|---------------------------------|----------------------------------------------------------------|
| Life Expectancy                 | 100,000 hours at $V_{RMS}$ with $T_{HS} \leq 75^\circ\text{C}$ |
| Capacitance Drop at End of Life | -5% (typical)                                                  |
| Failure Rate IEC 61709          | See FIT Graph                                                  |

## Test Methods

|                                 |                                                          |
|---------------------------------|----------------------------------------------------------|
| Test Voltage Term to Term (UTT) | $1.5 \times V_{RMS}$ for 10 seconds at 25°C              |
| Test Voltage Term to Case (UTC) | 3,600 V ~ 50 Hz for 10 seconds ( $V_{RMS} \leq 480$ VAC) |
|                                 | 6,000 V ~ 50 Hz for 10 seconds ( $V_{RMS} \geq 550$ VAC) |
| Damp Heat                       | IEC 60068-2-78                                           |
| Change of Temperature           | IEC 60068-2-14                                           |
| Vibration Strength              | IEC 60068-2-6                                            |


**NOTICE:** Care should be taken to ensure that there still is electrical clearance of 15 mm between terminations and other live or earthed parts above the capacitor, in case of safety device activation.

**Table 1 – Ratings & Part Number Reference**


| Cap Value (μF) | V <sub>rms</sub> | Rated Voltage | Surge Voltage | Maximum Dimensions (mm) |     | I <sub>rms</sub> at 10 kHz, 40°C | R <sub>s</sub> | ESL  | Thermal Resistance | dV/dt (V/μs) | Part Number     |
|----------------|------------------|---------------|---------------|-------------------------|-----|----------------------------------|----------------|------|--------------------|--------------|-----------------|
|                | VAC              | VDC           | VDC           | D                       | H   | (A) <sup>1</sup>                 | (mΩ)           | (nH) | (°C/W)             |              |                 |
| 100            | 330              | 700           | 1,050         | 65                      | 117 | 25                               | 2.3            | 115  | 8.5                | 12.5         | C44PLGR6100RASJ |
| 200            | 330              | 700           | 1,050         | 75                      | 117 | 43                               | 1.7            | 140  | 6.1                | 12.5         | C44PLGR6200RASJ |
| 300            | 330              | 700           | 1,050         | 65                      | 247 | 45                               | 2.0            | 150  | 3.6                | 12.5         | C44PLGR6300RASJ |
| 320            | 330              | 700           | 1,050         | 65                      | 247 | 55                               | 2.0            | 160  | 3.6                | 12.5         | C44PLGR6320RASJ |
| 400            | 330              | 700           | 1,050         | 75                      | 247 | 55                               | 1.7            | 160  | 3.0                | 12.5         | C44PLGR6400RASJ |
| 500            | 330              | 700           | 1,050         | 75                      | 247 | 58                               | 1.7            | 170  | 3.0                | 12.5         | C44PLGR6500RASK |
| 500            | 330              | 700           | 1,050         | 85                      | 197 | 63                               | 1.2            | 160  | 3.4                | 12.5         | C44PLGR6500RBSK |
| 600            | 330              | 700           | 1,050         | 85                      | 247 | 65                               | 1.5            | 180  | 2.9                | 12.5         | C44PLGR6600RASJ |
| 600            | 330              | 700           | 1,050         | 85                      | 280 | 75                               | 1.1            | 210  | 2.4                | 12.5         | C44PLGR6600RBSK |
| 100            | 440              | 1,000         | 1,500         | 75                      | 147 | 30                               | 2.7            | 145  | 5.7                | 20           | C44PKGR6100RASJ |
| 100            | 440              | 1,000         | 1,500         | 65                      | 197 | 50                               | 1.8            | 135  | 4.4                | 20           | C44PKGR6100RBSJ |
| 120            | 440              | 1,000         | 1,500         | 65                      | 197 | 50                               | 1.8            | 165  | 4.2                | 20           | C44PKGR6120RASK |
| 133            | 440              | 1,000         | 1,500         | 65                      | 247 | 40                               | 2.5            | 155  | 3.7                | 20           | C44PKGR6133RASJ |
| 133            | 440              | 1,000         | 1,500         | 75                      | 197 | 50                               | 1.6            | 170  | 4.0                | 20           | C44PKGR6133RBSJ |
| 150            | 440              | 1,000         | 1,500         | 65                      | 247 | 45                               | 2.3            | 160  | 3.5                | 20           | C44PKGR6150RASJ |
| 200            | 440              | 1,000         | 1,500         | 75                      | 247 | 55                               | 2.0            | 175  | 3.2                | 20           | C44PKGR6200RASJ |
| 250            | 440              | 1,000         | 1,500         | 85                      | 247 | 60                               | 1.7            | 175  | 3.1                | 20           | C44PKGR6250RASJ |
| 300            | 440              | 1,000         | 1,500         | 85                      | 247 | 60                               | 1.6            | 180  | 2.8                | 20           | C44PKGR6300RASK |
| 60             | 480              | 1,100         | 1,650         | 75                      | 117 | 35                               | 2.4            | 140  | 6.9                | 20           | C44PMGR5600RASJ |
| 60             | 480              | 1,100         | 1,650         | 65                      | 147 | 30                               | 3.8            | 140  | 5.9                | 20           | C44PMGR5600RBSJ |
| 70             | 480              | 1,100         | 1,650         | 75                      | 147 | 50                               | 1.4            | 145  | 5.7                | 20           | C44PMGR5700RASJ |
| 80             | 480              | 1,100         | 1,650         | 75                      | 147 | 50                               | 1.4            | 150  | 5.3                | 20           | C44PMGR5800RASJ |
| 100            | 480              | 1,100         | 1,650         | 75                      | 157 | 50                               | 1.2            | 160  | 5.0                | 20           | C44PMGR6100RASJ |
| 150            | 480              | 1,100         | 1,650         | 75                      | 197 | 50                               | 1.4            | 170  | 5.8                | 20           | C44PMGR6150RASK |
| 166            | 480              | 1,100         | 1,650         | 85                      | 197 | 55                               | 1.4            | 173  | 5.0                | 20           | C44PMGR6166RASJ |
| 200            | 480              | 1,100         | 1,650         | 75                      | 247 | 50                               | 1.8            | 175  | 4.6                | 20           | C44PMGR6200RASK |
| 250            | 480              | 1,100         | 1,650         | 85                      | 247 | 50                               | 1.6            | 180  | 4.2                | 20           | C44PMGR6250RASJ |
| 22             | 550              | 1,280         | 1,900         | 65                      | 117 | 34                               | 2.1            | 125  | 11.5               | 30           | C44PPGR5220RASK |
| 33             | 550              | 1,280         | 1,900         | 75                      | 117 | 40                               | 1.6            | 130  | 10.4               | 30           | C44PPGR5330RASK |
| 47             | 550              | 1,280         | 1,900         | 65                      | 197 | 50                               | 1.4            | 135  | 7.8                | 30           | C44PPGR5470RASK |
| 68             | 550              | 1,280         | 1,900         | 65                      | 247 | 50                               | 1.7            | 145  | 6.1                | 30           | C44PPGR5680RASK |
| 100            | 550              | 1,280         | 1,900         | 75                      | 247 | 57                               | 1.4            | 160  | 5.2                | 30           | C44PPGR6100RASK |
| 120            | 550              | 1,280         | 1,900         | 85                      | 247 | 60                               | 1.3            | 165  | 4.6                | 30           | C44PPGR6120RASK |
| 150            | 550              | 1,280         | 1,900         | 95                      | 247 | 60                               | 1.2            | 180  | 4.4                | 30           | C44PPGR6150RASK |
| 15             | 640              | 1,400         | 2,100         | 65                      | 117 | 30                               | 2.5            | 120  | 12.2               | 30           | C44PRGR5150RASK |
| 22             | 640              | 1,400         | 2,100         | 65                      | 147 | 30                               | 3.0            | 125  | 10.1               | 30           | C44PRGR5220RASK |
| 33             | 640              | 1,400         | 2,100         | 75                      | 147 | 36                               | 2.2            | 135  | 9.1                | 30           | C44PRGR5330RASK |
| 47             | 640              | 1,400         | 2,100         | 65                      | 247 | 49                               | 1.9            | 145  | 5.9                | 30           | C44PRGR5470RASK |
| 68             | 640              | 1,400         | 2,100         | 75                      | 247 | 55                               | 1.6            | 160  | 5.2                | 30           | C44PRGR5680RASK |
| 100            | 640              | 1,400         | 2,100         | 95                      | 247 | 60                               | 1.3            | 170  | 4.4                | 30           | C44PRGR6100RASK |
| 120            | 640              | 1,400         | 2,100         | 95                      | 247 | 60                               | 1.3            | 180  | 4.1                | 30           | C44PRGR6120RASK |
| 150            | 640              | 1,400         | 2,100         | 116                     | 247 | 60                               | 1.2            | 180  | 3.8                | 30           | C44PRGR6150RASK |
| 10             | 780              | 1,700         | 2,500         | 65                      | 117 | 25                               | 3.0            | 130  | 14.2               | 70           | C44PUGR5100RASK |
| 15             | 780              | 1,700         | 2,500         | 75                      | 147 | 28                               | 3.6            | 135  | 9.7                | 70           | C44PUGR5150RASK |
| 22             | 780              | 1,700         | 2,500         | 75                      | 147 | 35                               | 2.7            | 140  | 8.1                | 70           | C44PUGR5220RASK |
| 33             | 780              | 1,700         | 2,500         | 85                      | 147 | 42                               | 2.0            | 150  | 7.1                | 70           | C44PUGR5330RASK |
| 47             | 780              | 1,700         | 2,500         | 75                      | 247 | 52                               | 1.8            | 160  | 5.2                | 70           | C44PUGR5470RASK |
| 68             | 780              | 1,700         | 2,500         | 85                      | 247 | 55                               | 1.5            | 170  | 4.8                | 70           | C44PUGR5680RASK |
| 100            | 780              | 1,700         | 2,500         | 95                      | 247 | 60                               | 1.3            | 180  | 4.0                | 70           | C44PUGR6100RASK |
| 15             | 1,000            | 2,300         | 3,300         | 75                      | 147 | 32                               | 2.5            | 150  | 9.4                | 85           | C44PXGR5150RASK |
| 20             | 1,000            | 2,300         | 3,300         | 75                      | 140 | 36                               | 2.1            | 150  | 8.3                | 85           | C44PXGR5200RCSK |
| 22             | 1,000            | 2,300         | 3,300         | 75                      | 147 | 35                               | 2.0            | 155  | 8.0                | 85           | C44PXGR5220RASK |
| 33             | 1,000            | 2,300         | 3,300         | 75                      | 247 | 40                               | 1.7            | 165  | 5.3                | 85           | C44PXGR5330RASK |
| 47             | 1,000            | 2,300         | 3,300         | 85                      | 247 | 45                               | 1.4            | 170  | 4.7                | 85           | C44PXGR5470RASK |
| 68             | 1,000            | 2,300         | 3,300         | 95                      | 247 | 55                               | 1.2            | 180  | 4.1                | 85           | C44PXGR5680RASK |
| Cap Value      | VAC              | Rated Voltage | Surge Voltage | D                       | H   | I <sub>rms</sub>                 | R <sub>s</sub> | ESL  | Thermal Resistance | dV/dt (V/μs) | Part Number     |

<sup>1</sup> Maximum admissible RMS current  $T_{HS} \leq 75^{\circ}\text{C}$ ;  $\Delta T_{max} \leq 35^{\circ}\text{C}$ .

## Lifetime Expectancy/Failure Quota Graphs



$V$  = Operating Voltage [VAC]  
 $V_{rms}$  = Rated Voltage [VAC]



### Power Losses and Hot Spot Temperature Calculation

At each frequency, the Power Losses are the sum of:

1. Dielectric Power Losses

$$P_D(f) = 2 * \pi * f_i * C * V(f)^2 * \text{tg}\delta_0$$

which can be alternatively calculated as

$$P_D(f_i) = \frac{I(f_i)^2}{2 * \pi * f_i * C} * \text{tg}\delta_0$$

where:  $\text{tg}\delta_0 = 2 * 10^{-4}$

2. Joule Power Losses:

$$P_J(f) = R_s * I(f)^2$$

The Total Power Losses are the sum of the components at each frequency:

$$P_T = \sum_i [P_D(f_i) + P_J(f_i)]$$

The Thermal Jump in the Hot Spot is:

$$\Delta T_{HS} = P_T * R_{th-hs}$$

The Hot Spot Temperature is:

$$T_{HS} = T_a + \Delta T_{HS}$$

### Limits for the formulas

The limits listed below should not be exceeded:

- $\sqrt{\sum_i V(f_i)^2} \leq V_{RMS}$
- $\sqrt{\sum_i I(f_i)^2} \leq I_{RMS}$

$$T_{HS} = T_a + \Delta T_{HS} \leq (T_{HS})_{MAX}$$

Where  $T_a$  is the ambient temperature (steady state temperature of the cooling air flowing around the capacitor, measured at 100 mm of distance from the capacitor and at a height of 2/3 height of the capacitor).

3. Maximum case temperature ( $T_{CASE}$ ) ≤ 70°C

### Example of calculation

Part Number: C44PKGR6100RASJ

Rated  $V_{RMS} = 440$  [V<sub>RMS</sub>]

Rated  $I_{RMS} = 30$  [A]

$R_s = 2.7$  [mΩ]

$R_{th} = 5.7$  [°C/W]

Fundamental Frequency  $F_1 = 50$  [Hz]

Ripple Frequency  $F_2 = 7,000$  [Hz]

Fundamental Voltage  $V_1 = 440$  [V~]

Ripple Current  $I_2 = 27$  [A]

$T_a = 39^\circ\text{C}$

$I_1 = I(50) = 2 * \pi * 50 * 100 * 10^{-6} * 440 = 13.8$  [A]

$V_2 = V(7,000) = [27 / (2 * \pi * 7,000 * 100 * 10^{-6})] = 6.14$  [V]

$$I_{RMS} = \sqrt{(13.8^2 + 27^2)} = 30 \leq 30 \rightarrow \text{Admitted}$$

$$V_{RMS} = \sqrt{(440^2 + 6.1^2)} = 440 \leq 440 \rightarrow \text{Admitted}$$

$$P_D(50) = 2 * \pi * 50 * 100 * 10^{-6} * 440^2 * 2 * 10^{-4} = 1.22$$
 [W]

$$P_D(7,000) = [27^2 / (2 * \pi * 7,000 * 100 * 10^{-6})] * 2 * 10^{-4} = 0.03$$
 [W]

$$P_J(50) = 2.7 * 10^{-3} * [(2 * \pi * 50 * 100 * 10^{-6} * 440)^2] = 0.52$$
 [W]

$$P_J(7,000) = 2.7 * 10^{-3} * 27^2 = 1.97$$
 [W]

$$P_T = 1.22 + 0.03 + 0.52 + 1.97 = 3.74$$
 [W]

$$\Delta T_{HS} = 5.7 * 3.74 = 21$$
 [°C]

$$T_{HS} = T_a + \Delta T_{HS}$$

$$T_{HS} = 39 + 21 = 60$$
 [°C] → OK since hot spot temperature is less than maximum admitted

Expected Life at  $T_{HS} = 75^\circ\text{C} \rightarrow 100,000$  hours (see lifetime curve)

Expected Life at  $T_{HS} = 60^\circ\text{C} \rightarrow 140,000$  hours (see lifetime curve)

## Marking

|                                                                                                      |                                  |
|------------------------------------------------------------------------------------------------------|----------------------------------|
| KEMET                                                                                                | Manufacturer Logo                |
| C44PLGR6400RASJ                                                                                      | Part Number                      |
| 400 $\mu$ F $\pm$ 5%                                                                                 | Rated Capacitance and Tolerance  |
| Urms = 330V~                                                                                         | Rated Voltage                    |
| Irms = 55A 50/60Hz                                                                                   | Rated Current and Frequencies    |
| -25/70/56                                                                                            | Climatic Category                |
| PROTECTED 10000AFC  | UL Approvals                     |
| SH NO PCBs                                                                                           | Self-Healing Dielectric, UL Logo |
| BJ1 17340275                                                                                         | Production Date and Batch Number |

## Environmental Compliance

As a leading global supplier of electronic components and an environmentally conscious company, KEMET continually aspires to improve the environmental effects of our manufacturing processes and our finished electronic components.

In Europe (RoHS Directive) and in some other geographical areas such as China (China RoHS), legislation has been enacted to prevent or otherwise limit the use of certain hazardous materials, including lead (Pb), in electronic equipment. KEMET monitors legislation globally to ensure compliance and endeavors to adjust our manufacturing processes and/or electronic components as may be required by applicable law.

For military, medical, automotive, and some commercial applications, the use of lead (Pb) in the termination is necessary and/or required by design. KEMET is committed to communicating RoHS compliance to our customers. Information related to RoHS compliance will be provided in data sheets and using specific identifiers on the packaging labels.

All KEMET power film capacitors are RoHS compliant.

## Materials & Environment

The selection of raw materials that KEMET uses for the production of its electronic components is the result of extensive experience. KEMET directs specific attention toward environmental protection. KEMET selects its suppliers according to ISO 9001 standards and performs statistical analyses on raw materials before acceptance for use in manufacturing our electronic components. All materials are, to the best of KEMET's knowledge, non-toxic and free from cadmium; mercury; chrome and compounds; polychlorine triphenyl (PCB); bromide and chlorinedioxins bromurate clorurate; CFC and HCFC; and asbestos.

## Dissipation Factor

Dissipation factor is a complex function involved with capacitor inefficiency. The  $\tan \delta$  may vary up and down with increased temperature. For more information, refer to Performance Characteristics.

## Sealing

### Hermetically Sealed Capacitors

As the temperature increases, the pressure inside the capacitor increases. If the internal pressure is high enough, it can cause a breach in the capacitor. Such a breach can result in leakage, impregnation, filling fluid, or moisture susceptibility.

### Barometric Pressure

The altitude at which hermetically sealed capacitors are operated controls the capacitor's voltage rating. As the barometric pressure decreases, the susceptibility to terminal arc-over increases. Non-hermetic capacitors can be affected by internal stresses due to pressure changes. These effects can be in the form of capacitance changes, dielectric arc-over, and/or low insulation resistance. Altitude can also affect heat transfer. Heat that is generated in an operation cannot be dissipated properly, and high  $RI^2$  losses and eventual failure can result.

## KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit [www.kemet.com/sales](http://www.kemet.com/sales).

### Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

Additional information about production site flexibility can be found [here](#)

*KEMET is a registered trademark of KEMET Electronics Corporation.*