



Part Number : [26604090](#)

Product Description : KK 396 Header, Vertical, Friction Lock, 9 Circuits, Tin (Sn) Plating

Series Number : 41791

Status : Active

Product Category : PCB Headers and Receptacles

Engineering Part Number : 41791-0009



Documents and Resources

Drawings

[026604090_sd.pdf](#)

[PK-41791-001-001.pdf](#)

[026604090_stp.zip](#)


[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)6375-DC (05 Nov 2025) |
| EU RoHS | Compliant per EU 2015/863 |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|----------------|--|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 41791 |
| Description | KK 396 Header, Vertical, Friction Lock, 9 Circuits, Tin (Sn) Plating |
| Application | Power, Wire-to-Board |
| Component Type | PCB Header |
| Product Name | KK 396 |
| UPC | 800753585980 |

Agency

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Electrical

| | |
|-------------------------------|------------------|
| Current - Maximum per Contact | 7.0A |
| Voltage - Maximum | 600V AC (RMS)/DC |

Physical

| | |
|--------------------------------|---------|
| Breakaway | No |
| Circuits (Loaded) | 9 |
| Circuits (maximum) | 9 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 25 |

| | |
|-------------------------------|---------------------------|
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Resin | Polyester |
| Net Weight | 3.366/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Bag |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| PC Tail Length | 3.56mm |
| Pitch - Mating Interface | 3.96mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Partial |
| Stackable | Yes |
| Temperature Range - Operating | See Product Specification |
| Termination Interface Style | Through Hole |

Solder Process Data

| | |
|------------------------------|------|
| Max-Duration | 5 |
| Lead-Free Process Capability | WAVE |
| Max-Cycle | 1 |
| Max-Temp | 235 |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|-------------------------------------|-------------|
| KK 3.96mm Single Row Crimp Housings | <u>2139</u> |

| | |
|---|--------------|
| KK 3.96mm Single Row Crimp Housings | <u>3069</u> |
| KK 3.96mm Crimp Housings | <u>41695</u> |
| KK 396 PC Board Connector | <u>41815</u> |
| KK 3.96mm Pitch Single Row Crimp Housings | <u>6442</u> |

This document was generated on Dec 26, 2025