Part Number : 1200650265
Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 5.0m (16.40') Length
Series Number : 120065
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 804000A09M050



Documents and Resources

Drawings

1200650265_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33; 3; 47
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, A-Coded, Female (Straight) to Pigtail, 22 AWG, Yellow PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	78172553162

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.33mm (.210")
Cable Length	5.0m (16.40')

Downloaded from Arrow.com.

Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	197.400/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

Downloaded from Arrow.com.