




Home > Products > MICRO SWITCH™ Toggle Switches > TW > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

12TW75-3



TW Series Toggle Switch, 2 pole, 2 position, Solder T2 Type terminal, Standard Lever

Actual product appearance may vary.

Features

Save space and weight
SPDT and DPDT circuitry
Temperature range: -85° F to +160° F (-65° C to +71° C)
Sealed bushing versions
Choice of 7/16 in. or 15/32 in. bushing
Color tab available on 15/32 in. bushing
UL recognized

Potential Applications




Industrial machinery and equipment
Military and commercial aviation
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Description

MICRO SWITCH™ miniature toggle switches in two bushing sizes. Molded-in terminals are plated for soldering. Momentary and maintained circuitry closures available. Special on-on-on circuitries are also available. Pull-to-unlock levers prevent accidental operation.

Supporting Documentation

- [Accessory: Lever Sleeve](#)
- [Accessory: Seals](#)
- [Accessory: Nuts](#)
- [Engineering Drawing](#)

Product Specifications		
Circuitry/Operating action	Keyway Position	Opposite Keyway Position
		
		
Product Type	MICRO SWITCH™ Toggle Switch	
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc, 0.1 A to 5.0 A at 0.5 Vac to 115 Vac	
Circuitry	DPDT	
Action	2 position	
Mounting	Bushing 15/32 in	
Termination	Solder T2 type	
Lever Type	Standard	
UL/CSA Rating Code	L117: 5 A at 125 Vac	
Comment	Fine silver contacts	
Availability	Global	
UNSPSC Code	30211908	
UNSPSC Commodity	30211908 Toggle switches	
Series Name	TW	

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search