

Cable connector - CA-07S1N8AT006

1620285

<https://www.phoenixcontact.com/us/products/1620285>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Cable connector, CA, angled, shielded: yes, Screw locking, M23, No. of pos.: 7, Direction of rotation: Standard, type of contact: Socket, Crimp connection, cable diameter range: 4 mm ... 6 mm, coding:N



Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

Cable connector - CA-07S1N8AT006



1620285

<https://www.phoenixcontact.com/us/products/1620285>

Commercial Data

Item number	1620285
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	A12
Product Key	ABRBFB
Catalog Page	Page 92 (C-2-2019)
GTIN	4046356818018
Weight per Piece (including packing)	193.7 g
Weight per Piece (excluding packing)	193.7 g
Customs tariff number	85366990
Country of origin	DE

Cable connector - CA-07S1N8AT006



1620285

<https://www.phoenixcontact.com/us/products/1620285>

Technical Data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Connector

Insulating body

Application	Signal
Number of positions	7
Contact type	Socket
Coding	N
Connection method	Crimp connection
Connection profile	7
Direction of rotation	Standard
Material	PA 6.6

Housing

Type of locking	Screw locking
Thread type	M23
Degree of protection	IP67
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Seal material	NBR
External cable diameter	4 mm ... 6 mm

Cable connector - CA-07S1N8AT006


1620285

<https://www.phoenixcontact.com/us/products/1620285>



Drawings

Dimensional drawing



Cable connector - CA-07S1N8AT006



1620285

<https://www.phoenixcontact.com/us/products/1620285>

Approvals

cUL Recognized Approval ID: E335019-20141210				
	Nominal Voltage U _N	Nominal Current I _N	Cross Section AWG	Cross Section mm ²
	48 V	10 A	- 14	-

UL Recognized Approval ID: E335019-20141210				
	Nominal Voltage U _N	Nominal Current I _N	Cross Section AWG	Cross Section mm ²
	48 V	17 A	- 14	-

cULus Recognized				
------------------	--	--	--	--

Cable connector - CA-07S1N8AT006



1620285

<https://www.phoenixcontact.com/us/products/1620285>

Classifications

ECLASS

ECLASS-9.0	27440102
ECLASS-10.0.1	27440102
ECLASS-11.0	27440102

ETIM

ETIM 8.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Cable connector - CA-07S1N8AT006

1620285

<https://www.phoenixcontact.com/us/products/1620285>



Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Cable connector - CA-07S1N8AT006

1620285

<https://www.phoenixcontact.com/us/products/1620285>



Accessories

Protective cap

Protective cap - RC-Z2058 - 1604223

<https://www.phoenixcontact.com/us/products/1604223>

Plastic protection cap for connectors with M23 knurled nut



Plastic anti-static dust protection cap

Plastic anti-static dust protection cap - RC-Z2468 - 1611796

<https://www.phoenixcontact.com/us/products/1611796>

Plastic protection cap, antistatic, for connectors with M23 knurled nut



Cable connector - CA-07S1N8AT006

1620285

<https://www.phoenixcontact.com/us/products/1620285>



Metal protective cap

Metal protective cap - CA-Z0077 - 1627224

<https://www.phoenixcontact.com/us/products/1627224>



Metal protection cap with steel wire and loop, for M23 signal connectors with knurled nut for fastening to the cable

Torque screwdriver

Torque screwdriver - SF-Z0028 - 1607456

<https://www.phoenixcontact.com/us/products/1607456>



Torque screwdriver, series: RC

Cable connector - CA-07S1N8AT006

1620285

<https://www.phoenixcontact.com/us/products/1620285>



Hook wrench

Hook wrench - SF-Z0027 - 1607455

<https://www.phoenixcontact.com/us/products/1607455>



Hook wrench, series: RC

Color-coding

Color-coding - RF-Z0014 - 1620588

<https://www.phoenixcontact.com/us/products/1620588>



Color-coding, color: green

Cable connector - CA-07S1N8AT006



1620285

<https://www.phoenixcontact.com/us/products/1620285>

Color-coding

Color-coding - RF-Z0015 - 1620592

<https://www.phoenixcontact.com/us/products/1620592>

Color-coding, color: orange



Color-coding

Color-coding - RF-Z0016 - 1620593

<https://www.phoenixcontact.com/us/products/1620593>

Color-coding, color: black



Cable connector - CA-07S1N8AT006



1620285

<https://www.phoenixcontact.com/us/products/1620285>

Crimp contact

Crimp contact - RC-5CS2000 - 1603517

<https://www.phoenixcontact.com/us/products/1603517>



Crimp contact, turned, contact diameter: 2 mm, crimp range: 1 mm² ... 1.5 mm²

Crimp contact

Crimp contact - RC-5AS2000 - 1603509

<https://www.phoenixcontact.com/us/products/1603509>



Crimp contact, turned, contact diameter: 2 mm, crimp range: 1.5 mm² ... 2.5 mm²

Cable connector - CA-07S1N8AT006

1620285

<https://www.phoenixcontact.com/us/products/1620285>



Crimp contact

Crimp contact - RC-5SS2000 - 1603530

<https://www.phoenixcontact.com/us/products/1603530>



Crimp contact, turned, contact diameter: 2 mm, crimp range: 0.5 mm² ... 0.75 mm²

Crimp contact

Crimp contact - RC-59S2000 - 1603501

<https://www.phoenixcontact.com/us/products/1603501>



Crimp contact, turned, Single contact, contact diameter: 2 mm, crimp range: 0.75 mm² ... 1 mm²

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com