**Part Number :** 734155030
**Product Description :** SMP Jack, Right-Angle, Crimp, RG-174, RG-188 and RG-316 Cable, Brass Body, 0.25µm Gold (Au) Plated, 80 Pieces Per Tray, 50 Ohms
**Series Number :** 73300
**Status :** Active
**Product Category :** RF / Coaxial Connectors



## Documents and Resources

### Drawings

734155030_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

896789980-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | RF / Coaxial Connectors |
| Series | 73300 |
| Description | SMP Jack, Right-Angle, Crimp, RG-174, RG-188 and RG-316 Cable, Brass Body, 0.25µm Gold (Au) Plated, 80 Pieces Per Tray, 50 Ohms |
| Application | RF |
| Product Name | SMP |
| Style | Cable |
| Type | Microminiature |
| UPC | 822350417532 |

### Electrical

| | |
|---|---|
| Frequency | 40 GHz |
| Impedance | 50Ω |
| Power / Voltage | VOLTAGE: 335 Vrms@Sea Level |

### Physical

| | |
|---|---|
| Cable Attachment | Crimp |
| Gender | Jack |
| Keying to Mating Part | N/A |
| Net Weight | 1.226/g |
| Orientation | Right Angle |
| Packaging Type | Tray |

Downloaded from Arrow.com.

| | |
|---|---|
| Panel Mount | No |
| Panel Mount Method | N/A |
| PCB Mounting | N/A |
| Reverse Polar | No |
| Wire/Cable Type | LMR-100, RG-174, RG-188, RG-316 |

## Solder Process Data

| | |
|---|---|
| Lead-Free Process Capability | N/A |



Downloaded from Arrow.com.