6A, 400V - 1000V Standard Bridge Rectifier

FEATURES

- Ideal for printed circuit board
- High surge current capability
- Typical I_R less than 0.1μA
- UL Recognized File # E-326243
- AEC-Q101 available
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS


- Switching mode power supply (SMPS)
- Adapters
- TV
- Monitor

MECHANICAL DATA


- Case: TS4K
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Mounting torque: 8.17 in-lbs maximum
- Weight: 4.00g (approximately)

KEY PARAMETERS		
PARAMETER	**VALUE**	**UNIT**
I_F	6	A
V_{RRM}	400 - 1000	V
I_{FSM}	150	A
$T_{J\ MAX}$	150	°C
Package	TS4K	
Configuration	Quad	

Pb-Free RoHS COMPLIANT HALOGEN FREE



TS4K



ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)							
PARAMETER		**SYMBOL**	**TS6K40**	**TS6K60**	**TS6K80**	**TS6K100**	**UNIT**
Marking code on the device			TS6K40	TS6K60	TS6K80	TS6K100	
Repetitive peak reverse voltage		V_{RRM}	400	600	800	1000	V
Reverse voltage, total rms value		$V_{R(RMS)}$	280	420	560	700	V
Forward current		I_F	6				A
Surge peak forward current single half sine-wave superimposed on rated load per diode	t = 8.3ms	I_{FSM}	150				A
Rating of fusing (t<8.3ms)		I^2t	93				A^2s
Junction temperature		T_J	- 55 to +150				°C
Storage temperature		T_{STG}	- 55 to +150				°C

Downloaded from Arrow.com.

THERMAL PERFORMANCE			
PARAMETER	**SYMBOL**	**TYP**	**UNIT**
Junction-to-case thermal resistance	$R_{\Theta JC}$	3	°C/W

ELECTRICAL SPECIFICATIONS (T_A = 25°C unless otherwise noted)					
PARAMETER	**CONDITIONS**	**SYMBOL**	**TYP**	**MAX**	**UNIT**
Forward voltage per diode(1)	I_F = 3A, T_J = 25°C	V_F	-	1.0	V
	I_F = 6A, T_J = 25°C		-	1.1	V
Reverse current @ rated V_R per diode(2)	T_J = 25°C	I_R	-	5	μA
	T_J =125°C		-	500	μA

Notes:

1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms

ORDERING INFORMATION		
ORDERING CODE(1)(2)	**PACKAGE**	**PACKING**
TS6Kx	TS4K	20 / Tube
TS6KxH	TS4K	20 / Tube

Notes:

1. “x” defines voltage from 400V(TS6K40) to 1000V(TS6K100)
2. “H” means AEC-Q101 qualified

Downloaded from Arrow.com.

CHARACTERISTICS CURVES

(T_A = 25°C unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-repetitive Forward Surge Current



Downloaded from Arrow.com.

PACKAGE OUTLINE DIMENSIONS

TS4K



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.40	4.80	0.173	0.189
A1	3.40	3.80	0.134	0.150
A2	3.10	3.40	0.122	0.134
b	0.90	1.10	0.035	0.043
b2	2.00	2.30	0.079	0.091
c	0.50	0.70	0.020	0.028
D	14.70	15.30	0.579	0.602
D2	9.30	9.60	0.366	0.378
D3	3.00	5.00	0.118	0.197
E	24.70	25.30	0.972	0.996
e	7.30	7.70	0.287	0.303
L	17.00	18.00	0.669	0.709
L4	3.30	3.70	0.130	0.146
P	3.10	3.60	0.122	0.142

MARKING DIAGRAM



P/N = Marking Code
G = Green Compound
YWW = Date Code
F = Factory Code

Downloaded from Arrow.com.

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Downloaded from Arrow.com.