

Product data sheet

Specifications



12' CABLE EXTENDER 5-WIRE #10 AWG, UL WITH L21-20R/P

PDW12L21-20XC

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	120 V 208 V 3 phases
Input Connection Type	NEMA L21-20P
Cable length	3.7 m
Number of cables	1
Provided equipment	Installation guide

Physical

Height	6.4 cm
Width	5.1 cm
Depth	365.8 cm
Net weight	1.82 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Permissible voltage	200...240 V
Max line current	20 A

Output

Max current draw	20 A
------------------	------

Conformance

Product certifications	UL listed
------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	10.2 cm
Package 1 Width	44.5 cm
Package 1 Length	30.5 cm
Package 1 Weight	2.05 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

