5x25mm/ No. 240



Indicator, 250V

Time-Current Characteristic
Quick Acting (F)

Standard
None

Approvals
None

Specifications

Packaging
002: Pack (100 pcs.)

Materials
Tube: Ceramic
End Caps: Nickel-plated brass

Operating Temperature
-25ºC to +70ºC (consider de-rating)


Climatic Category
-25°C/+70°C/21 days (EN 60068-1..3)

Stock Conditions
+10ºC to +60ºC
relative humidity ≤ 75% yearly average, without dew

Vibration Resistance
24 cycles at 15 min. each (EN 60068-2-6)
10 - 60Hz at 0.75mm amplitude
60 - 2000Hz at 10g acceleration

Marking
Ⓦ, F, Current Rating, 250V

Dimensions (mm)



Limits for Pre-arcing Time				
Rated Current	1.5 x I_{Rated}	2.1 x I_{Rated}	4 x I_{Rated}	10 x I_{Rated}
1.60A ... 6.3A	> 1h	< 30 min	< 300ms	< 20ms

Permissible continuous operating current is 100 % at ambient temperature of 23ºC (73.4ºF).

Rated Current	Amp Code	Voltage Rating	Breaking Capacity	Voltage Drop 1.0 x I_{Rated} Ⓦ max. (mV)	Power Dissipation 1.5 x I_{Rated} Ⓦ max. (W)	Melting Integral 10 x I_{Rated} Ⓦ max. (A^2s)	color of indicator
1.6A	1160	250V[1]	1500A @ 250 V AC 50Hz cos φ = 0.7	640	on request	1.3	orange
2.0A	1200	250V[1]		420		2.5	blue
2.5A	1250	250V[1]		320		5.8	yellow
4.0A	1400	250V[1]		200		21.0	brown
6.3A	1630	250V[1]		170		78.0	green

[1] Operating Voltage ≥ 10 V

Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.

Order Information


Qty.	Order-Number	Series	Amp Code	Packaging
		240		

WICKMANN Ⓦ

In our continuing strategy to deliver unparalleled circuit protection solutions, technical expertise and application leadership, we proudly introduce the WICKMANN Group and its products to the Littelfuse portfolio.

Downloaded from Arrow.com.

5x25mm/ No. 240



Contact Littelfuse for individual I-t curves

WICKMANN

In our continuing strategy to deliver unparalleled circuit protection solutions, technical expertise and application leadership, we proudly introduce the WICKMANN Group and its products to the Littelfuse portfolio.

Downloaded from Arrow.com.