



Data Sheet | Item Number: 289-424

Interface module; Pluggable connector per DIN 41612; 32-pole; Mating connector for solder connection; Vertical mounting; PCB terminal blocks, double-row; with mounting feet; Type C; 2,50 mm²

<https://www.wago.com/289-424>



Notes	
Safety Information	Notice! Live parts can be easily touched! Protection against direct contact must be provided by the equipment manufacturer, e.g., using a WAGO 709 Series Cover (see "Accessories") or a similar cover. The installation guidelines must be observed for each individual application.

Electrical data	
Operating voltage	≤ 30 VAC; ≤ 50 VDC
Nominal current	1 A
Contact resistance (max.)	20 mΩ

Safety and protection	
Rated Voltage	50 V
Rated impulse withstand voltage	0.8 kV
Pollution degree	2
Protection type	IP00

Connection data	
Performance level	2 / 400 mating cycles
Connection 1	
Pluggable connector	Pluggable connector per DIN 41612; Type C; Male connector
Pole number 1	32
Connection type 1	System
Note (conductor cross-section)	12 AWG: THHN, THWN
Mating direction	vertical

Connection 2	
Design 2	PCB terminal blocks (double-row)
Pole number 2	32
Connection type	Field
Connection technology	CAGE CLAMP®
WAGO connector 2	WAGO 236 Series
Solid conductor	0.08 ... 2.5 mm ² / 28 ... 12 AWG

Connection 2	
Fine-stranded conductor	0.08 ... 2.5 mm ² / 28 ... 12 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches



Physical data		
Width		97 mm / 3.819 inches
Height		63.5 mm / 2.5 inches
Depth from upper-edge of DIN-rail		21 mm / 0.827 inches

Mechanical data		
Mounting type		DIN-35 rail
Housing design		PCB with mounting feet

Material data		
Contact material (connector)		Copper alloy; gold plated
Fire load		0.056 MJ
Weight		62.1 g

Environmental requirements		
Ambient temperature (operation)		-20 ... +50 °C
Ambient temperature (storage)		-40 ... +70 °C
Relative humidity		≤ 85 % (non-condensing)

Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		15 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4066966387568
Customs tariff number		85369010000

Product classification		
UNSPSC		39121402
eCl@ss 10.0		27-14-11-52
eCl@ss 9.0		27-14-11-52
ETIM 9.0		EC002780
ETIM 8.0		EC002780
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 289-424

Download icon

Documentation

Bid Text

289-424

19.02.2019

xml

3.44 KB

Download icon

289-424

09.02.2015

doc

26.00 KB

Download icon

Instruction Leaflet

Operation and Assembly Instructions Interface

V 1.0.0

02.04.2025

pdf

1246.19 KB

Download icon

CAD/CAE-Data

CAE data

EPLAN Data Portal 289-424

Download icon

WSCAD Universe 289-424

Download icon

1 Compatible Products

1.1 Optional Accessories

1.1.1 Installation

1.1.1.1 Cover



Item No.: 709-153
Cover; Type 1; suitable for cover carrier, type 1; 1 m long; transparent

1.1.1.2 Cover carrier

Item No.: 709-167
Cover carrier; Type 1; incl. fixing/retaining screws and knurled nut; suitable for 279 to 282 and 880 Series rail-mounted terminal blocks; suitable for 264 Series miniature rail-mounted terminal blocks; suitable for 270 Series sensor and actuator terminal blocks; gray

1.1.2 Tool


1.1.2.1 Operating tool




Item No.: 210-720
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Installation Notes

Conductor termination



Conductor termination – screwdriver ac-
tuation parallel to conductor entry



Conductor termination – screwdriver ac-
tuation perpendicular to conductor entry