

Integrated Magnetic, Stacked (Mag45™) and Power over Ethernet (PoE)



Active

- ? Gigabit Ethernet Application
- ? Component Type = Single Port
- ? Magnetic Circuit = 4G01P1
- ? Turns Ratio = 1:1
- ? 1 x 1 Jack Configuration

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

(PDF, English)

? None Available

? [Mag45* Modular Jacks With Integrated Magnetics](#) (PDF, English)

? None Available

? None Available

? None Available

? Product Line Information

? Tooling

List all Documents

Product Type Features:

- ? Signal Routing Type = Auto MDI/MDIX
- ? PCB Mount Style = Thru Hole
- ? Shielded = Yes
- ? Shield Material = Brass

? Jack Configuration = 1 x 1

? Impedance (?) = 100

? Component Type = Single Port

? Turns Ratio = 1:1

? Bottom Panel Ground Tab = Without

- ? LED = With
- ? Shield Panel Ground Tabs = With
- ? Latch Orientation = Standard - Latch Down
- ? Bottom Shield = Without
- ? Shield Plating = Semi -Bright Nickel (Pre -plated)

? Housing Flammability Rating = UL 94V -0

- ? Magnetic Circuit = 4G01P1
- ? Decoupling Capacitor = 2KV
- ? Rear PCB Ground Tab = Without
- ? Signal Lead Quantity = 10

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

- ? Left LED Color (Position #1) = Green/Yellow (Bicolor)
- ? Right LED Color (Position #2) = Green/Yellow (Bicolor)

? Temperature Rating = Office / Premises (0 °C to +70 °C)

? Application = Gigabit Ethernet

? Insulator = Without

? Brand = Transpower