



Part Number : [2244511114](#)
Product Description : Pre-Crimped Lead Stac64
Female-to-Stac64 Female, Tin (Sn) Plating, 300.00mm
Length, 0.75mm² Wire, Black
Series Number : 224451
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents and Resources

Drawings
[2244511114 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224451
Description	Pre-Crimped Lead Stac64 Female-to-Stac64 Female, Tin (Sn) Plating, 300.00mm Length, 0.75mm ² Wire, Black
Application	Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Stac64 Crimp Terminals
Product Name	Stac64
UPC	196823398209

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	14V DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.292/g
Number of Rows	1
Packaging Type	Bag

Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	FLR2X-A
Wire Size mm ²	0.75

This document was generated on May 19, 2026