




Part Number : [417920515](#)
Product Description : KK 396 Header, Right-Angle with Friction Lock, 6 Circuits, 0.38µm Gold (Au) Selective Plating
Series Number : 41792
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings
[417920515_sd.pdf](#)
[PK-41792-002-001.pdf](#)

3D Models and Design Files
[417920515_stp.zip](#)
[SYM-26-60-5060-001.zip](#)

Specifications
[PS-08-50-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	41792
Description	KK 396 Header, Right-Angle with Friction Lock, 6 Circuits, 0.38µm Gold (Au) Selective Plating
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	KK 396
UPC	822348062317

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No

Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	2.856/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Bag
PC Tail Length	3.96mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.96mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	Yes
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	<u>2139</u>

KK 3.96mm Single Row Crimp Housings	<u>3069</u>
KK 3.96mm Crimp Housings	<u>41695</u>
KK 396 PC Board Connector	<u>41815</u>
KK 3.96mm Pitch Single Row Crimp Housings	<u>6442</u>

This document was generated on Mar 08, 2025