



PART NUMBER	LED COLOR
595-2101-002	RED
595-2101-007	
595-2101-013	
595-2201-002	HI. INTENSITY GREEN
595-2201-007	
595-2201-013	
595-2301-002	GREEN
595-2301-007	
595-2301-013	
595-2401-002	YELLOW
595-2401-007	
595-2401-013	
595-2501-002	ORANGE
595-2501-007	
595-2501-013	
595-2701-002	AlInGaP YELLOW
595-2701-007	
595-2701-013	

OPERATING CHARACTERISTICS AT 25°C AMBIENT							
CHARACTERISTICS		MIN	TYP	MAX	UNITS	TEST CONDITIONS	
LUMINOUS INTENSITY	RED		25.0		mcd	I _f = 20 mA	
	GREEN		11.0				
	YELLOW		9.0				
	ORANGE		9.0				
FORWARD VOLTAGE	RED		1.7	2.0	V	I _f = 20 mA	
	GREEN		2.1	2.5			
	YELLOW		2.2	2.5			
	ORANGE		2.2	2.5			
REVERSE VOLTAGE	RED	4			V	I _s = 100 µA	
	GREEN	4					
	YELLOW	4					
	ORANGE	4					
PEAK WAVELENGTH	RED		660		nm		
	GREEN		560				
	YELLOW		580				
	ORANGE		605				

OPERATING CHARACTERISTICS AT 25°C AMBIENT							
CHARACTERISTICS		MIN	TYP	MAX	UNITS	TEST CONDITIONS	
LUMINOUS INTENSITY	HI. INT. GREEN		8.5		mcd	I _f = 10 mA	
	AlInGaP YELLOW		41.0				
FORWARD VOLTAGE	HI. INT. GREEN		2.2	2.6	V	I _f = 20 mA	
	AlInGaP YELLOW		2.02	2.4			
REVERSE CURRENT	HI. INT. GREEN			100	µA	V _r = 5 V	
	AlInGaP YELLOW			100			
PEAK WAVELENGTH	HI. INT. GREEN		566		nm		
	AlInGaP YELLOW		592				

ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT			
POWER DISSIPATION	HI. INT. GREEN	65	mW
	AlInGaP YELLOW	81	
DERATE LINEARLY FROM 75°C (* FROM 55°C)	HI. INT. GREEN	0.75	mA/°C
	AlInGaP YELLOW	0.58 *	
CONTINUOUS FORWARD CURRENT	HI. INT. GREEN	25	mA
	AlInGaP YELLOW	30	
OPERATING TEMPERATURE		ALL	-30 TO 85 °C
STORAGE TEMPERATURE		ALL	-40 TO 100 °C
INFRARED REFLOW SOLDERING		ALL	240°C FOR 10 SEC


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	---	NEW RELEASE	YY	---	NO	4-28-93
B	---	REDRAWN WITH CHANGES NEW HSG AND LENS DESIGN	YY	---	NO	2-7-94
C	---	CHANGE LUM. INT 25.0 WAS 9.5 (RED), 9.0 WAS 5.7 (YEL) 11.0 WAS 5.6 (GRN)	YY	---	NO	3-28-94
D	---	ADDED HI. GREEN AND AlInGaP YELLOW ADD NOTE 6	AV	DC	NO	3-8-00
E	---	ADDED NOTE 7. "PLACE MOIS- TURE SENSITIVE LEVEL '2a' LABEL....VACUUM SEAL BAG."	DC	KD	NO	2-9-01
F	---	ADDED P/N 595-2501-002, 595-2501-007,595-2501-013 AND NOTE 8. REVISED NOTE 5 ...7 INCH REEL, 600 PCS/REEL WAS 400; ...13 INCH REEL, 2300 PCS/REEL WAS 1600.	DC	AM	N.O.	3-14-02
G	---	ADDED NOTE 9 LENS INSPECTION PROCEDURE;UPDATED FORMAT;	TWC			




ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT			
POWER DISSIPATION	RED	60	mW
	GREEN	75	
	YELLOW	75	
	ORANGE	75	
DERATE LINEARLY FROM 25°C	RED,GRN,YEL	0.42	mA/°C
CONTINUOUS FORWARD CURRENT	RED,GRN,YEL,ORANGE	30	mA
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE WIDTH)	RED,GRN,YEL,ORANGE	70	mA
OPERATING TEMPERATURE	RED,GRN,YEL,ORANGE	-30 TO +85	°C
STORAGE TEMPERATURE	RED,GRN,YEL	-30 TO 80	°C
	ORANGE	-40 TO +100	°C
INFRARED REFLOW SOLDERING	RED,GRN,YEL	235°C FOR 15 SEC	
VAPOR PHASE SOLDERING	RED,GRN,YEL	215°C FOR 3 MIN	

NOTES :


- 1- MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY
- 2- PAD NUMBERS ARE FOR REFERENCE ONLY , DESIGNATION NON-EXISTENT ON PART
- 3- STORAGE CONDITIONS FOR TAPED PRODUCT: RE-TAPING MAY BE NECESSARY FOR PRODUCTS STORED MORE THAN TWELVE MONTHS
- 4- ORDER QUANTITY IS LED ASSEMBLIES , NOT REELS
- 5- ...-002 SUFFIX MEANS PARTS ARE PACKED ON A 20 pc SAMPLE STRIP
...-007 SUFFIX MEANS PARTS ARE PACKED ON A 7 INCH REEL , 600 pcs/REEL
...-013 SUFFIX MEANS PARTS ARE PACKED ON A 13 INCH REEL , 2300 pcs/REEL
- 6- DIALIGHT PART NUMBERS =
595-2x01-002 595-2x01-007 595-2x01-013
- 7- PLACE MOISTURE-SENSITIVE LEVEL "2a" LABEL ON 595-2201-007,595-2201-013,
595-2701-007,595-2701-013. LEVEL "4" LABEL ON 595-2101-007,595-2101-013,
595-2301-007,595-2301-013,595-2401-007,595-2401-013, 595-2501-007,
595-2501-013. VACUUM SEAL BAG.
- 8- PACKAGING ONE HUMIDITY INDICATOR CARD(9100-999-0662-99) PER BAG.
- 9- PER LENS INSPECTION PROCEDURE 01-225 THIS AREA CAN HAVE PORTIONS MISSING OF UP TO 50%. NON-CRITICAL AREA BELOW LENS.




TAPING SPECIFICATION



TOLERANCE: .004 UNLESS OTHERWISE SPECIFIED
MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY



13 INCH DIA. REEL SPECIFICATIONS



7 INCH DIA. REEL SPECIFICATIONS

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.		
SCALE: DRAWING SCALE	DRAWING NUMBER	REV
ALL DIM'S IN: INCHES (MM)	C-15637	G
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE SURFACE MOUNT CB1	
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005 DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL	
FINISH:	Dialight	
FSCM 83330	1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727	
SHEET 1 OF 1	FAMILY TABLE:	