



ELECTRO-OPTICAL CHARACTERISTICS		Ta=25°C	If=20mA
PARAMETER	MIN	TYP	MAX
OPERATING VOLTAGE	90		115
STARTING VOLTAGE (AC)			95
STARTING VOLTAGE (DC)			135
OPERATING CURRENT		1.7	
LIGHT OUTPUT		65	
LIFE HOURS		20,000	

1. EXTERNAL RESISTOR VALVE 33k OHMS
2. LEAD LENGTH 25mm MIN.
3. LEAD SPACING 2mm TYP
4. MINIMUM VALUE IS NOT GUARANTEED.
5. LEAD FINISH IS TO BE SHINY TIN COATING.

UNCONTROLLED DOCUMENT



NEON LAMP, T-4mm HIGH BRIGHTNESS, TIN COATING.

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT.

CONFIDENTIAL INFORMATION

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE: 08.24.11	DRAWN BY: AB
PAGE: 1 OF 1	CHKD BY: KF
SCALE: NTS	APRVD BY: SS
UNIT: mm [INCH]	