

CK1,6-ED-1,50BU AG - Crimp contact



1663433

<https://www.phoenixcontact.com/us/products/1663433>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

Commercial data

Item number	1663433
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	BF7AIA
Catalog page	Page 507 (C-2-2019)
GTIN	4017918123246
Weight per piece (including packing)	0.675 g
Weight per piece (excluding packing)	0.663 g
Customs tariff number	85366990
Country of origin	DE

CK1,6-ED-1,50BU AG - Crimp contact



1663433

<https://www.phoenixcontact.com/us/products/1663433>

Technical data

Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
---------	--

Mounting

Assembly note	At voltages of < 5 V and currents < 5 mA, gold-plated contacts are recommended.
	The quality of a crimp connection is determined by DIN EN 60352-2.

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
	HC-M-08-MBIT
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	1.5 mm ² ... 1.5 mm ²
Connection cross section AWG	16
Stripping length of the individual wire	8 mm
Conductor cross section flexible	1.5 mm ² ... 1.5 mm ²

Material specifications

Contact material	Copper alloy
Contact surface material	silver-plated

Dimensions

Mechanical characteristics

CK1,6-ED-1,50BU AG - Crimp contact



1663433

<https://www.phoenixcontact.com/us/products/1663433>

Contact diameter	1.6 mm
------------------	--------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ED-1,50BU AG - Crimp contact




1663433

<https://www.phoenixcontact.com/us/products/1663433>

Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-1,50BU AG - Crimp contact



1663433

<https://www.phoenixcontact.com/us/products/1663433>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1663433>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC

Approval ID: EAC-Zulassung

CK1,6-ED-1,50BU AG - Crimp contact



1663433

<https://www.phoenixcontact.com/us/products/1663433>

Classifications

ECLASS

ECLASS-11.0	27440204
ECLASS-12.0	27440204
ECLASS-13.0	27440204

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-1,50BU AG - Crimp contact



1663433

<https://www.phoenixcontact.com/us/products/1663433>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	56de65b7-4627-45c6-9d4b-61546a92d8ee

CK1,6-ED-1,50BU AG - Crimp contact

1663433

<https://www.phoenixcontact.com/us/products/1663433>



Accessories

CK1,6-ED-1,50ST AG - Crimp contact

1663378

<https://www.phoenixcontact.com/us/products/1663378>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm² ... 1.5 mm², AWG 16

CRIMPFOX-TC MP-6 - Crimping pliers with digital display

1202888

<https://www.phoenixcontact.com/us/products/1202888>



Crimping tool, for turned contacts, universal cross-section setting, up to a maximum of 6.0 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, positioning tool necessary as an accessory for contact positioning

CK1,6-ED-1,50BU AG - Crimp contact

1663433

<https://www.phoenixcontact.com/us/products/1663433>



CRIMPFOX-TC HC 4 - Crimping pliers

1297083

<https://www.phoenixcontact.com/us/products/1297083>



Crimping pliers, for CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

UNIFOX RT-CK 1.6 - Contact removal tool

1072069

<https://www.phoenixcontact.com/us/products/1072069>



Contact removal tool, for turned and rolled CK- 1.6-... contacts

CK1,6-ED-1,50BU AG - Crimp contact

1663433

<https://www.phoenixcontact.com/us/products/1663433>



UNIFOX MT-CK 1.6/2.5 - Assembly tool

1089092

<https://www.phoenixcontact.com/us/products/1089092>




Assembly tool, for CK 1.6... crimp contacts for small conductor cross sections

CF 500/DIE TC HC 4 - Crimp insert

1324132

<https://www.phoenixcontact.com/us/products/1324132>



Die for CF 500 automatic crimping device, CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com