




N° of contacts	Part number	A	B	C	D	E
006	15 15 006 x601 xxx	2,54	6,96	8,89	5,76	4,76
008	15 15 008 x601 xxx	3,81	8,23	10,16	7,03	6,03
010	15 15 010 x601 xxx	5,08	9,50	11,43	8,30	7,30
012	15 15 012 x601 xxx	6,35	10,77	12,70	9,57	8,57
014	15 15 014 x601 xxx	7,62	12,04	13,97	10,84	9,84
016	15 15 016 x601 xxx	8,89	13,31	15,24	12,11	11,11
018	15 15 018 x601 xxx	10,16	14,58	16,51	13,38	12,38
020	15 15 020 x601 xxx	11,43	15,85	17,78	14,65	13,65
022	15 15 022 x601 xxx	12,70	17,12	19,05	15,92	14,92
024	15 15 024 x601 xxx	13,97	18,39	20,32	17,19	16,19
026	15 15 026 x601 xxx	15,24	19,66	21,59	18,46	17,46
028	15 15 028 x601 xxx	16,51	20,93	22,86	19,73	18,73
030	15 15 030 x601 xxx	17,78	22,20	24,13	21,00	20,00
032	15 15 032 x601 xxx	19,05	23,47	25,40	22,27	21,27
034	15 15 034 x601 xxx	20,32	24,74	26,67	23,54	22,54
036	15 15 036 x601 xxx	21,59	26,01	27,94	24,81	23,81
038	15 15 038 x601 xxx	22,86	27,28	29,21	26,08	25,08
040	15 15 040 x601 xxx	24,13	28,55	30,48	27,35	26,35
042	15 15 042 x601 xxx	25,40	29,82	31,75	28,62	27,62
044	15 15 044 x601 xxx	26,67	31,09	33,02	29,89	28,89
046	15 15 046 x601 xxx	27,94	32,36	34,29	31,16	30,16
048	15 15 048 x601 xxx	29,21	33,63	35,56	32,43	31,43
050	15 15 050 x601 xxx	30,48	34,90	36,83	33,70	32,70
052	15 15 052 x601 xxx	31,75	36,17	38,10	34,97	33,97
054	15 15 054 x601 xxx	33,02	37,44	39,37	36,24	35,24
056	15 15 056 x601 xxx	34,29	38,71	40,64	37,51	36,51
058	15 15 058 x601 xxx	35,56	39,98	41,91	38,78	37,78
060	15 15 060 x601 xxx	36,83	41,25	43,18	40,05	39,05
062	15 15 062 x601 xxx	38,10	42,52	44,45	41,32	40,32
064	15 15 064 x601 xxx	39,37	43,79	45,72	42,59	41,59
066	15 15 066 x601 xxx	40,64	45,06	46,99	43,86	42,86
068	15 15 068 x601 xxx	41,91	46,33	48,26	45,13	44,13
070	15 15 070 x601 xxx	43,18	47,60	49,53	46,40	45,40
072	15 15 072 x601 xxx	44,45	48,87	50,80	47,67	46,67
074	15 15 074 x601 xxx	45,72	50,14	52,07	48,94	47,94
076	15 15 076 x601 xxx	46,99	51,41	53,34	50,21	49,21
078	15 15 078 x601 xxx	48,26	52,68	54,61	51,48	50,48
080	15 15 080 x601 xxx	49,53	53,95	55,88	52,75	51,75
082	15 15 082 x601 xxx	50,80	55,22	57,15	54,02	53,02
084	15 15 084 x601 xxx	52,07	56,49	58,42	55,29	54,29
086	15 15 086 x601 xxx	53,34	57,76	59,69	56,56	55,56
088	15 15 088 x601 xxx	54,61	59,03	60,96	57,83	56,83
090	15 15 090 x601 xxx	55,88	60,30	62,23	59,10	58,10
092	15 15 092 x601 xxx	57,15	61,57	63,50	60,37	59,37
094	15 15 094 x601 xxx	58,42	62,84	64,77	61,64	60,64
096	15 15 096 x601 xxx	59,69	64,11	66,04	62,91	61,91
098	15 15 098 x601 xxx	60,96	65,38	67,31	64,18	63,18
100	15 15 100 x601 xxx	62,23	66,65	68,58	65,45	64,45

Packaging	
tape & reel with 560 pcs per reel	000
samples	333

Performance level	
PL1: >500 mating cycles	2
PL2: >250 mating cycles	6
PLS4: min. 0,06µm Au over 0,7+0,2µm PdNi	5

	All Dimensions in mm Original Size DIN A3		Scale 5:1	Free size tol.		Ref.	
	All rights reserved		Created by ZHUANGJ	Inspected by LUOK	Standardisation HOFFMANN	Date 2020-06-19	State Final Release
Department EL PD		Title har-flex angled male connector		Doc-Key / ECM-Nr. 100223537/UGD/008/D 500000171593		Rev. D	
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 1515XXX601XXX		Page 1/1		