


Data Sheet | Item Number: 770-515/021-000

Strain relief housing; 5-pole; for 1 cable; 11.5 ... 16.5 mm; 71 mm; white

<https://www.wago.com/770-515/021-000>



Color: ■ white



Dimensions in mm

Strain relief housing *WINSTA*® MIDI 5-pole

Implement the energy supply quickly and easily: The strain relief housing from the *WINSTA*® MIDI product line is the solution for error-free electrical installation. A comprehensive range of accessories complements the *WINSTA*® product line from WAGO. Our *WINSTA*® MIDI product line achieves maximum flexibility for the installation of applications. With its Push-in *CAGE CLAMP*® spring pressure connection technology, it guarantees error-free, time-saving installation and offers flexibility and customization for meeting all installation requirements. The strip length is 71 mm.

Lower costs through fast commissioning and elimination of service expenses – solutions from *WINSTA*® MIDI

The *WINSTA*® Pluggable Connection System is perfectly tailored to the strict requirements of building installation. It makes electrical installation pluggable, and consequently faster, more reliable, and error-free. Using this pre-assembled system decreases time spent on assembly and installation errors at the construction site. Take advantage of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with with protection against mismatching from WAGO.

- pre-assembled versions
- quick replacement of defective units during ongoing operation

Notes

General safety information

NOTICE: Observe installation and safety instructions!

1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100).
2. Do not install while energized or under load.
3. Use only for its intended purpose.
4. Observe applicable national regulations, standards and directives.
5. Observe the technical specifications of the products.
6. Ensure correct polarity assignment.
7. Do not use damaged or contaminated components.
8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters.
9. Insert conductors up to the stop.
10. Use only with locking lever and strain relief.
11. Use original accessories only.

To be sold only with installation instructions!

Connection Data

Connection 1

Pole number	5
Connectable sheathed cable diameter	11.5 ... 16.5 mm
Strip length (outer insulation)	71 mm

Physical data

Pin spacing	10 mm / 0.394 inches
Width	54.75 mm / 2.156 inches
Height	21 mm / 0.827 inches
Depth	72.7 mm / 2.862 inches

Mechanical data

Screw tightening torque	0.5 Nm
-------------------------	--------

Material data

Note (material data)	Information on material specifications can be found here
Color	white
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.499 MJ
Weight	19.9 g

Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

PU (SPU)	25 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454026240
Customs tariff number	85389099990

Product Classification

UNSPSC	39121722
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
cURus Underwriters Laboratories Inc.	UL 1977	E45171
VDE VDE Prüf- und Zertifizierungsinstitut	EN 61535	40029808

Downloads





Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 770-515/021-000	↓

Documentation

Bid Text			
770-515/021-000	19.02.2019	xml 2.84 KB	↓
770-515/021-000	10.12.2014	doc 24.00 KB	↓

CAD/CAE-Data

CAD data	CAE data
2D/3D Models 770-515/021-000 	EPLAN Data Portal 770-515/021-000 
	WSCAD Universe 770-515/021-000 
	ZUKEN Portal 770-515/021-000 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marking strip



Item No.: 210-333

Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive; white