Part Number : 1200678461
Product Description : M12 Signal, A-Coded, Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (90°) to Pigtail with LED for PNP Sensors, 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
Series Number : 120067
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 8040P1B30M050



Documents and Resources

Drawings

1200678461_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120067
Description	M12 Signal, A-Coded, Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (90°) to Pigtail with LED for PNP Sensors, 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Single Ended
UPC	889056091374

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC/DC

Physical

Cable Diameter	5.10mm (.201")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded, Knurled Hexnut
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	PNP Sensors
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass

Downloaded from Arrow.com.

Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215, WSOR
Wire Size (AWG)	22

Downloaded from Arrow.com.