

Free Search

Search

Search Items

LEDs Manufacturers

-choose-

LEDs

-choose-

Product ranges

-choose-

Diameter (mm)

-min- -max-

Side (mm)

-min- -max-

Height (mm)

-min- -max-

Material

-choose-

Viewing Angle (FWHM) ...

-min- -max-

... or select angle from list

-choose-

Type of Optics

-choose-

Single vs Multi Optics

-choose-

Connector

-choose-

Application required

-choose-

Required Application

Search Items

Reset all search items



Description
Ultra Clear Silicone Lenses for LG 17W COB LEDs
100,00mm x 111,00mm side - 33,11mm height
Type IV

BENEFITS:

- Lenses material: Silicone
- Ring Material: PC
- Full angle at 50%: ~ 150° x 155°
- Full angle at 10%: ~ 165° x 165°
- The light spots here represented refer to tests carried out with CoBs with 23mm LES, ~5225lm

SIO3 Silicone Lens is supplied without the holder. The holder is optional and will be supplied only on request under the KE177614 (Material: PC) part number or under the KE177614ALU (Material: Aluminium) part number.
SIO3 Silicone Lens is supplied without the holder with connector. The holder with connector by Bender-Wirth is optional, available only on request.

----- Part Number -----

PL1771SR [SIO3 Silicone Lens Type IV]
PL1771SR + KE177614 [SIO3 Silicone Lens Type IV + Holder in PC material]
PL1771SR + KE177614ALU [SIO3 Silicone Lens Type IV + Holder in Aluminium material]

Why now a lens made of SILICONE?

The LEDs of latest generation - High Brightness LEDs and COB LEDs - achieve very high temperatures which could put strain on the conventional polymers such as PMMA, PMMA and PC. The typical features of silicone make silicone lenses perfect for outdoor applications or indoor applications in damp and wet environments:

- High temperature resistant; considerably reduce the yellowing effect.
- NO need for extra protection: glass or gasket for IP.
- As an isotropic material, silicone provides the lenses with high flexibility allowing easy fit to the final application.
- As an elastomer, silicone provides the lens with an excellent compensation capability that well meets the requirements of construction mechanical tolerances in the final application.

Optimized for most popular HB LEDs and COB LEDs. Designed for Street Light applications, comply with IESNA Standards: Type I - Type II - Type III - Type IV - Type V, Short or Medium light distribution depending on the LED used; M3a. Excellent in any application in Wide Area Lighting, Outdoor and Indoor. Preserve and enhance the typical characteristics of silicone. Optic type: FREE FORM LENSES, engineered by using new optical techniques; manufactured by using the latest in cold injection-moulding.

Beam Angles: 1 rotosymmetrical, 3 asymmetric, 1 axiallysymmetrical in x, y (rectangular spot). Optic Features: excellent transparency; high optical efficiency; no birefringence; high temperature resistant; flexibility at low temperatures; UV-resistant; no yellowing effect; easy fit to the final application; no need for extra protection such as glass or gasket for IP in case of head-pole; micro-crack resistant under harsh environmental conditions; immersion-proof; explosion-proof.

Product images are for illustrative purposes only.
All the data contained in this page are the property of Khatod Optoelectronic Srl and may change without prior notice.
Only the Part Numbers stated in Khatod order confirmations are the valid and active ones.


Accessories

Box for PCB and Electronic Components
Cover for Reflectors
Heatsinks
PCB for testing
Protective Lens for Seoul® Acriche2

Certifications & Statement

ISO 9001:2008 Certifications
RoHS Compliance
REACH Compliance
Conflict Mineral Statement
KHATOD LENS Use and Maintenance

Reserved Area
Versione 1.9.6_ev3_u4_B



Download Area [Download all files >>](#)

pl1771sr sio3 silicone lenses product brief
 pl1771sr technical detail
 pl1771sr 17w lg iesna
 pl1771sr 17w lg eulumdat

Samples Request **Quotations Request** **E-mail**

Tweet