

CT2676ARA

100 MHz Passive Oscilloscope Probe

Fixed 10x attenuation, readout actuator, 5 mm, cable...

Description

General purpose series 100 MHz, 10x fixed attenuation oscilloscope probe. Probe features a readout actuator pin (sense pin) on the BNC connector.

- 100 MHz (-3 dB) bandwidth
- High impedance input (10 megaohms/16 pF)
- 1035 pF compensation range
- 300 V CAT II

Features & Benefits:

- Snap-Locking Sprung Hook
- Easily replaceable tip
- Large accessory set
- Meets IEC 61010-031
- RoHS compliant

Accessories included: 15 cm Ground Lead, Replacement Tip, Black Snap-on Sprung Hook, Tip Insulator, IC Tip, BNC Adapter, Probe Tip Ground, Trimmer Tool & Identifier Rings.

The HighPerformance family is a high quality, general purpose set of 5mm Passive Voltage Oscilloscope probes. They are excellent replacement probes for all makes and models of oscilloscopes.

Datasho



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Type	5 mm Passive Voltage
Bandwidth	100 MHz
Attenuation	10x
Input Impedance	10 megaohms
Input Capacitance	16 pF
Output Impedance, ohm	1 megaohms
Risetime	3.5 ns
IEC Rating	300 V CAT II
Compensation	1035 pF
Cable Length	1.2 m
Readout Actuator	
Operating Temperature (degrees)	0 to +50 C
Humidity	85% RH or less (at 35 C)
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

