

MOSFET

600V CoolMOS™ CM8 Power Transistor

PG-LHSOF-4



The CoolMOS™ 8th generation platform is a revolutionary technology for high voltage power MOSFETs, designed according to the superjunction (SJ) principle and pioneered by Infineon Technologies. The 600V CoolMOS™ CM8 series is the successor to the CoolMOS™ 7.
It combines the benefits of a fast switching SJ MOSFET with excellent ease of use, e.g low ringing tendency, implemented fast body diode (CFD) for all products with outstanding robustness against hard commutation and excellent ESD capability. Furthermore, extremely low switching and conduction losses of CM8, make switching applications even more efficient.



Features

- Suitable for hard and soft switching topologies thanks to an outstanding commutation ruggedness
- Significant reduction of switching and conduction losses
- Best in class $R_{DS(on)}$ per package products enabled by ultra low $R_{DS(on)}$*A

Benefits

- Ease of use and fast design-in through low ringing tendency and usage across PFC and PWM stages
- Simplified thermal management thanks to our advanced die attach technique
- Increased power density solutions enabled by using products with smaller footprint and higher manufacturing quality due state of the art ESD protection
- Suitable for a wide variety of applications and power ranges

MOSFET; CoolMOS; SMPS; AI; Power Supply

Potential applications

- Power supplies and converters
- PFC stages & LLC resonant converters
- High efficiency switching applications
- e.g. Server, Telecom, EV Charging, UPS

Product validation

Fully qualified according to JEDEC for Industrial Applications

Please note: For MOSFET paralleling the use of ferrite beads on the gate or separate totem poles is generally recommended.

Table 1 Key Performance Parameters

Parameter	Value	Unit
V_{DS} @ $T_{j,max}$	650	V
$R_{DS(on),max}$	180	mΩ
$Q_{g,typ}$	17	nC
$I_{D,pulse}$	48	A
E_{oss} @ 400V	2.4	µJ
Body diode di_F/dt	1300	A/µs
ESD class (HBM)	2	-

Type / Ordering Code	Package	Marking	Related Links
IPTA60R180CM8	PG-LHSOF-4	60R180C8	see Appendix A

Downloaded from Arrow.com.

Table of Contents

Description 1
Maximum ratings 3
Thermal characteristics 4
Electrical characteristics 5
Electrical characteristics diagrams 7
Test Circuits 11
Package Outlines 12
Appendix A 13
Revision History 14
Trademarks 14
Disclaimer 14

Downloaded from Arrow.com.

1 Maximum ratings

at T_j = 25°C, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Continuous drain current[1)]	I_D	- -	- -	18 11	A	T_C=25°C T_C=100°C
Pulsed drain current[2)]	$I_{D,pulse}$	-	-	48	A	T_C=25°C
Avalanche energy, single pulse	E_{AS}	-	-	28	mJ	I_D=2.7A; V_{DD}=50V; see table 10
Avalanche energy, repetitive	E_{AR}	-	-	0.14	mJ	I_D=2.7A; V_{DD}=50V; see table 10
Avalanche current, single pulse	I_{AS}	-	-	2.7	A	-
MOSFET dv/dt ruggedness	dv/dt	-	-	120	V/ns	V_{DS}=0...400V
Gate source voltage (static)	V_{GS}	-20	-	20	V	static;
Gate source voltage (dynamic)	V_{GS}	-30	-	30	V	AC (f>1 Hz)
Power dissipation	P_{tot}	-	-	119	W	T_C=25°C
Storage temperature	T_{stg}	-55	-	150	°C	-
Operating junction temperature	T_j	-55	-	150	°C	-
Extended operating junction temperature	T_j	150	-	175	°C	≤50 h in the application lifetime
Mounting torque	-	-	-	-	Ncm	-
Continuous diode forward current	I_S	-	-	18	A	T_C=25°C
Diode pulse current[2)]	$I_{S,pulse}$	-	-	48	A	T_C=25°C
Reverse diode dv/dt[3)]	dv/dt	-	-	70	V/ns	V_{DS}=0...400V, I_{SD}≤18A, T_j=25°C see table 8
Maximum diode commutation speed	di_F/dt	-	-	1300	A/µs	V_{DS}=0...400V, I_{SD}≤18A, T_j=25°C see table 8
Insulation withstand voltage	V_{ISO}	-	-	n.a.	V	V_{rms}, T_C=25°C, t=1min

[1)] Limited by $T_{j,max}$.
[2)] Pulse width t_p limited by $T_{j,max}$
[3)] Identical low side and high side switch with identical R_G

Downloaded from Arrow.com.

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	1.05	K/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	62	K/W	device on PCB, minimal footprint
Thermal resistance, junction - ambient for SMD version	R_{thJA}	-	35	45	K/W	Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70µm thickness) copper area for drain connection and cooling. PCB is vertical without air stream cooling.
Soldering temperature, wave- & reflow soldering allowed	T_{sold}	-	-	260	°C	reflow MSL1

Downloaded from Arrow.com.

3 Electrical characteristics

at T_j=25°C, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	600	-	-	V	V_{GS}=0V, I_D=1mA
Gate threshold voltage	$V_{(GS)th}$	3.7	4.2	4.7	V	V_{DS}=V_{GS}, I_D=0.14mA
Zero gate voltage drain current	I_{DSS}	- -	- 20.8	1 -	µA	V_{DS}=600V, V_{GS}=0V, T_j=25°C V_{DS}=600V, V_{GS}=0V, T_j=150°C
Gate-source leakage current	I_{GSS}	-	-	1.6	µA	V_{GS}=20V, V_{DS}=0V
Drain-source on-state resistance	$R_{DS(on)}$	- -	0.150 0.331	0.180 -	Ω	V_{GS}=10V, I_D=5.6A, T_j=25°C V_{GS}=10V, I_D=5.6A, T_j=150°C
Gate resistance	R_G	-	12	-	Ω	f=1MHz

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	743	-	pF	V_{GS}=0V, V_{DS}=400V, f=250kHz
Output capacitance	C_{oss}	-	11	-	pF	V_{GS}=0V, V_{DS}=400V, f=250kHz
Effective output capacitance, energy related[1)]	$C_{o(er)}$	-	30	-	pF	V_{GS}=0V, V_{DS}=0...400V
Effective output capacitance, time related[2)]	$C_{o(tr)}$	-	301	-	pF	I_D=constant, V_{GS}=0V, V_{DS}=0...400V
Turn-on delay time	$t_{d(on)}$	-	17.2	-	ns	V_{DD}=400V, V_{GS}=13V, I_D=2.8A, R_G=10.0Ω; see table 9
Rise time	t_r	-	6	-	ns	V_{DD}=400V, V_{GS}=13V, I_D=2.8A, R_G=10.0Ω; see table 9
Turn-off delay time	$t_{d(off)}$	-	88.4	-	ns	V_{DD}=400V, V_{GS}=13V, I_D=2.8A, R_G=10.0Ω; see table 9
Fall time	t_f	-	12.8	-	ns	V_{DD}=400V, V_{GS}=13V, I_D=2.8A, R_G=10.0Ω; see table 9

Table 6 Gate charge characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	5	-	nC	V_{DD}=400V, I_D=2.8A, V_{GS}=0 to 10V
Gate to drain charge	Q_{gd}	-	6	-	nC	V_{DD}=400V, I_D=2.8A, V_{GS}=0 to 10V
Gate charge total	Q_g	-	17	-	nC	V_{DD}=400V, I_D=2.8A, V_{GS}=0 to 10V
Gate plateau voltage	$V_{plateau}$	-	6.1	-	V	V_{DD}=400V, I_D=2.8A, V_{GS}=0 to 10V

[1)] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 400V
[2)] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 400V

Downloaded from Arrow.com.


Table 7 Reverse diode characteristics

Parameter	Symbol	Values			Unit	Note / Test Condition
		Min.	Typ.	Max.		
Diode forward voltage	V_{SD}	-	0.9	-	V	V_{GS}=0V, I_F=2.8A, T_j=25°C
Reverse recovery time	t_{rr}	-	62.0	77	ns	V_R=400V, I_F=2.8A, di_F/dt=100A/µs; see table 8
Reverse recovery charge	Q_{rr}	-	0.18	0.27	µC	V_R=400V, I_F=2.8A, di_F/dt=100A/µs; see table 8
Peak reverse recovery current	I_{rrm}	-	6.0	-	A	V_R=400V, I_F=2.8A, di_F/dt=100A/µs; see table 8

Downloaded from Arrow.com.


4 Electrical characteristics diagrams

Diagram 1: Power dissipation




$P_{tot}=f(T_C)$

Diagram 2: Safe operating area




$I_D=f(V_{DS})$; $T_C=25$ °C; $D=0$; parameter: t_p

Diagram 3: Safe operating area



$I_D=f(V_{DS})$; $T_C=80$ °C; $D=0$; parameter: t_p


Diagram 4: Max. transient thermal impedance



$Z_{thJC}=f(t_P)$; parameter: $D=t_p/T$


Downloaded from Arrow.com.

Diagram 5: Typ. output characteristics




$I_D=f(V_{DS})$; $T_j=25$ °C; parameter: V_{GS}

Diagram 6: Typ. output characteristics




$I_D=f(V_{DS})$; $T_j=125$ °C; parameter: V_{GS}

Diagram 7: Typ. drain-source on-state resistance



$R_{DS(on)}=f(I_D)$; $T_j=125$ °C; parameter: V_{GS}


Diagram 8: Drain-source on-state resistance



$R_{DS(on)}=f(T_j)$; $I_D=5.6$ A; $V_{GS}=10$ V


Downloaded from Arrow.com.

Diagram 9: Typ. transfer characteristics




I_D=f(V_{GS}); V_{DS}=20V; parameter: T_j

Diagram 10: Typ. gate charge




V_{GS}=f(Q_{gate}); I_D=2.8 A pulsed; parameter: V_{DD}

Diagram 11: Forward characteristics of reverse diode



I_F=f(V_{SD}); parameter: T_j


Diagram 12: Avalanche energy



E_{AS}=f(T_j); I_D=2.7 A; V_{DD}=50 V


Downloaded from Arrow.com.

Diagram 13: Drain-source breakdown voltage




$V_{BR(DSS)}$=f(T_j); I_D=1 mA

Diagram 14: Typ. capacitances



C=f(V_{DS}); V_{GS}=0 V; f=250 kHz

Diagram 15: Typ. Coss stored energy



E_{oss}=f(V_{DS})

Downloaded from Arrow.com.

5 Test Circuits

Table 8 Diode characteristics



Test circuit for diode characteristics	Diode recovery waveform
	

Table 9 Switching times (ss)






Switching times test circuit for inductive load	Switching times waveform
	

Table 10 Unclamped inductive load (ss)

Unclamped inductive load test circuit	Unclamped inductive waveform
	

Downloaded from Arrow.com.

6 Package Outlines



PACKAGE - GROUP NUMBER:	PG-LHSOF-4-U01	
DIMENSIONS	**MILLIMETERS**	
	MIN.	MAX.
A	1.40	1.60
b	0.90	1.10
b1	7.46	7.66
b2	0.42	0.50
c	0.40	0.60
D	6.59	6.99
D1	2.30	
E	7.80	8.20
E1	6.66	
E2	7.56	
e	2.00	
N	4	
H	7.80	8.20
H1	4.30	
H2	2.57	
H3	1.65	
L	0.50	1.00
L1	0.51	
L2	0.23	
L3	0.50	0.90

Figure 1 Outline PG-LHSOF-4, dimensions in mm

Downloaded from Arrow.com.

7 Appendix A

Table 11 Related Links

- **IFX CoolMOS CM8 Webpage:** www.infineon.com
- **IFX CoolMOS CM8 application note:** www.infineon.com
- **IFX CoolMOS CM8 simulation model:** www.infineon.com
- **IFX Design tools:** www.infineon.com

Downloaded from Arrow.com.

Revision History

IPTA60R180CM8

Revision: 2024-03-21, Rev. 2.1

Previous Revision

Revision	Date	Subjects (major changes since last revision)
2.0	2024-03-15	Release of final version
2.1	2024-03-21	Update of R_{thJC}

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments
Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to:
erratum@infineon.com

Published by
Infineon Technologies AG
81726 München, Germany
© 2023 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”) .

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.
In addition, any information given in this document is subject to customer’s compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer’s products and any use of the product of Infineon Technologies in customer’s applications.
The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer’s technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information
For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Downloaded from Arrow.com.