


Color: white

Similar to illustration



Dimensions in mm
3) Drilled hole diameter: 4.2 mm
4) Drilled hole diameter: 5.2 mm
Drilled hole for direct PE contact must be free of varnish and oxide films.
Equipped with varnished metal plates upon request.

- Flexible, modular 5- to 11-pole connector system
- Future system expansions possible
- Compact design

Electrical data

Ratings per	IEC/EN 60664-1			Ratings per IEC/EN 2	
Overvoltage category	III	III	II	Rated current 2	6 A
Pollution degree	3	2	2		
Nominal voltage	-	500 V	-		
Rated surge voltage	-	4 kV	-		
Rated current	-	16 A	-		

Connection data

Number of connection types	1	Connection 1	
		Strip length	11 ... 12 mm / 0.43 ... 0.47 inches
		Pole number	3

Physical data

Width	39.1 mm / 1.539 inches
Height from the surface	19 mm / 0.748 inches



Material data		
Note (material data)		Information on material specifications can be found here
Color		white
Material group		I
Insulation material		Polyamide (PA66)
Flammability class per UL94		V0
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E _{Cu})
Contact plating		Tin
Fire load		0.111 MJ
Weight		14.8 g

Environmental requirements		
Temperature stability		105 °C

Commercial data		
eCl@ss 10.0		27-44-03-14
eCl@ss 9.0		27-44-03-14
ETIM 8.0		EC000458
PU (SPU)		50 pcs
Packaging type		Box
Country of origin		PL
GTIN		4045454415440
Customs tariff number		85366990990

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
UL UL International Germany GmbH	UL 1977	E45171
VDE VDE Prüf- und Zertifizierungsinstitut	EN 61984	40032309



Downloads			
Environmental Product Compliance			
Compliance Search			
Environmental Product Compliance 267-313			↓

Documentation			
Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	↓

CAD/CAE-Data			
CAD data		CAE data	
2D/3D Models 267-313		ZUKEN Portal 267-313	↓