





Data Sheet | Item Number: 858-324

Relay module; Nominal input voltage: 24 VDC; 2 changeover contacts; Limiting continuous current: 12 A; with manual operation; Red status indicator; Module width: 31 mm; 1,50 mm²

<https://www.wago.com/858-324>



DC load limit curve

Technical data			
Control circuit		Load circuit	
Nominal input voltage U _N	24 VDC	Number of changeover/switchover contacts	2
Input voltage range	-20 ... +10 %	Contact material (relay)	AgNi
Nominal input current at U _N	38 mA	Limiting continuous current	12 A
		Inrush current (resistive) max.	(AC) 24 A / 4 s
		Switching Voltage, Max.	250 VAC
		Switching power (resistive) max.	AC 3000 VA; DC (see load limit curve)
		Switching capacity	AC-15: 1.5 A / 240 VAC; DC-13: 0.1 A / 250 VDC
		Recommended minimum load	10 V / 5 mA / 300 mW
		Pull-in time (typ.)	13 ms
		Drop-out time (typ.)	3 ms
		Electrical life (NO; resistive load; 23 °C)	100 x 10³ switching operations
		Mechanical life	20 x 10⁶ switching operations
		Switching frequency with/without load (max.)	20 min⁻¹ / 200 min⁻¹



Signaling	
Status indicator	Red LED Mechanical

Safety and protection	
Rated Voltage	300 V
Rated impulse withstand voltage	2.5 kV
Overvoltage category	II
Pollution degree	2
Dielectric strength (control/load circuit) (AC, 1 min)	2.5 kVrms
Dielectric strength (open contact) (AC, 1 min)	1.5 kVrms
Dielectric strength (load/load circuit) (AC, 1 min)	2.5 kVrms
Insulation type (control/load circuit)	Basic insulation
Insulation type (open contact)	Functional insulation
Insulation type (load/load circuit)	Basic insulation
Insulation type (adjacent devices)	Reinforced insulation (safe isolation)
Protection type	IP20

Connection data	
Connection technology	Push-in CAGE CLAMP®
Solid conductor	0.34 ... 1.5 mm² / 22 ... 16 AWG
Fine-stranded conductor	0.34 ... 1.5 mm² / 22 ... 16 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 inches
Note (conductor cross-section)	2 x 0.34 ... 2 x 1.5 mm² / 1 x 2.5 mm² / 2 x 22 ... 2 x 16 AWG

Physical data	
Width	31 mm / 1.22 inches
Height	97 mm / 3.819 inches
Depth from upper-edge of DIN-rail	73 mm / 2.874 inches

Mechanical data	
Mounting type	DIN-35 rail
Mounting position	horizontal (standing/lying); vertical

Material data	
Note (material data)	Information on material specifications can be found here
Fire load	1.278 MJ
Weight	87.5 g

Environmental requirements	
Ambient temperature (operation at U _N)	-40 ... +55 °C
Ambient temperature (storage)	-40 ... +85 °C
Processing temperature	-25 ... +50 °C
Temperature range of connection cable	≥ (T _{ambient} + 25 K)
Relative humidity	5 ... 85 %
Operating altitude (max.)	2000 m



Standards and specifications		
Standards/specifications	EN 61010-2-201 EN 61810-1 UL 508	

Basic relay		
WAGO Basic Relay	858-181	

Commercial data		
Product Group	6 (INTERFACE ELECTRONIC)	
PU (SPU)	5 pcs	
Packaging type	Box	
Country of origin	DE	
GTIN	4055143567732	
Customs tariff number	85364900990	

Product classification		
UNSPSC	39122334	
eCl@ss 10.0	27-37-16-01	
eCl@ss 9.0	27-37-16-01	
ETIM 9.0	EC001437	
ETIM 8.0	EC001437	
ECCN	NO US CLASSIFICATION	

Environmental Product Compliance		
RoHS Compliance Status	Compliant,No Exemption	

Approvals / Certificates			
General approvals		Declarations of conformity and manufacturer's declarations	
			
	Approval	Standard	Certificate Name
	EAC	TP TC 004/2011	EAC CoC 03084
GZO Almaty Standart			
		</	



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 858-324

Download icon

Documentation

Bid Text

858-324	19.02.2019	xml 4.90 KB	Download icon
858-324	20.02.2019	docx 17.51 KB	Download icon

Instruction Leaflet

Stecksockel für Elementarrelais	V 2.0.0 25.01.2022	pdf 2130.02 KB	Download icon
---------------------------------	-----------------------	-------------------	---------------

CAD/CAE-Data

CAD data

2D/3D Models 858-324

Download icon

CAE data

EPLAN Data Portal 858-324

Download icon

WSCAD Universe 858-324

Download icon

ZUKEN Portal 858-324

Download icon

1 Compatible Products

1.1 Optional Accessories

1.1.1 Ferrule

1.1.1.1 Ferrule



[Item No.: 216-241](#)
Ferrule; Sleeve for 0.5 mm² / 20 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; white



[Item No.: 216-242](#)
Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray



[Item No.: 216-243](#)
Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red



[Item No.: 216-244](#)
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

1.1.2 Indicators

1.1.2.1 Status indication



[Item No.: 788-120](#)
Accessories for relay modules; Operation status indicator: red; Nominal operating voltage: 24 VDC



1.1.3 Installation

1.1.3.1 Ejector



[Item No.: 858-110](#)
Ejector; for basic relays 25 mm x 35 mm

1.1.4 Jumper

1.1.4.1 Jumper



[Item No.: 858-402](#)
Jumper; 2-way; insulated; light blue

1.1.5 Marking

1.1.5.1 Double marker carrier



[Item No.: 209-128](#)
Adaptor; gray

1.1.5.2 Group marker carrier



[Item No.: 249-105](#)
Group marker carrier; gray



[Item No.: 209-145](#)
Group marker carrier; white

1.1.5.3 Marker



[Item No.: 209-183](#)
Marker; white



[Item No.: 793-5501](#)
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



[Item No.: 793-502](#)
WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white



[Item No.: 793-566](#)
WMB marking card; as card; MARKED; 1 ... 50 (2x); not stretchable; Horizontal marking; snap-on type; white



[Item No.: 793-503](#)
WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white



[Item No.: 793-504](#)
WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white



[Item No.: 793-505](#)
WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white



[Item No.: 793-506](#)
WMB marking card; as card; MARKED; 41 ... 50 (10x); not stretchable; Horizontal marking; snap-on type; white



[Item No.: 793-501](#)
WMB marking card; as card; not stretchable; plain; snap-on type; white



[Item No.: 2009-115](#)
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.5.4 Marking device



Item No.: 210-110
Fiber-tip pen

1.1.5.5 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel;
not stretchable; plain; snap-on type; white

1.1.5.6 Protective marker cover



Item No.: 209-184
Protection cover; transparent

1.1.6 Tool



1.1.6.1 Operating tool



Item No.: 210-719
Operating tool; Blade: 2.5 x 0.4 mm; with a
partially insulated shaft

Installation Notes

Commoning



Removing a jumper via screwdriver.

Marking



Marking using WMB Multi markers and
group marker carriers.