


4

3

2


1

LOC	DIST	REVISIONS				
AJ	16	P	LTR	DESCRIPTION	DATE	APVD
			AJ2	REVISED PER ECO-10-008433	24MAY10	HMR KW



1. COPPER ALLOY
2. TIN-LEAD PLATE PER ASTM-B-545, 2.54 μm [.000100] MIN THICKNESS, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.
3. SILVER PLATE PER QQ-S-365, 5.08 μm [.000200] MIN THICKNESS
4. SEE SEPARATE RESTRICTED CUSTOMER DRAWING FOR THIS PART NUMBER
5. MATTE TIN PLATE 2.54 μm [.000100] MINIMUM THICKNESS, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT
6. BRIGHT TIN PLATE 2.54 μm [.000100] MINIMUM THICKNESS, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT

4	OBSOLETE	6.35 [.250]	3	50428-9
	OBSOLETE	6.35 [.250]	3	50428-8
		6.35 [.250]	2	50428-6
		6.55 [.258]	2	50428-2
		6.55 [.258]	3	50428-1
		∅A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.E. COWHER 2-17-92	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK J.T. LIPPERT 2-25-92	NAME FERRULE, HEAVY WALL					
	0 PLC ± -	APVD M. PHILLIPS 2-25-92						
	1 PLC ± -	PRODUCT SPEC						
	2 PLC ± 0.38[.015]	APPLICATION SPEC						
	3 PLC ± -	—						
4 PLC ± -	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL SEE NOTE 1	FINISH SEE TABLE	WEIGHT —	A3	00779	C-50428	—		
CUSTOMER DRAWING			SCALE	8:1	SHEET	1 OF 1	REV	AJ2