



Automotive Parts > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Number of Positions: 2

Primary Product Color: **Black**

Connector & Contact Retention Accessory Type: **Retainer**

Primary Product Material: **PBT GF10**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

Sealable	No
Connector & Contact Retention Accessory Type	Retainer

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF10

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Box
Packaging Quantity	6000

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-1587987-3  
RECEPTACLE ASSEMBLY, 250A, MSD



TE Part # 1299428-1  
CABLE ASSY-LV HVIL EXTN(ASM-001748)



TE Part # 2315855-4  
MSD,REC HSG ASSY,450A,V0,M8



TE Part # 1-1587987-4  
FUSE,RECEPTACLE ASSEMBLY, 630A, MSD



TE Part # CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING



TE Part # 2315855-6  
MSD,REC HSG ASSY,630A,V0,M8



Customers Also Bought



TE Part #CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING



TE Part #8-963964-4  
ACTION PIN FOR 1 mm HOLE



TE Part #1355390-1  
JUN-POW-TIM GEH 2P



TE Part #6-1355688-7  
MT3-REC. HOUSING, 6 POS.



TE Part #1534184-2  
MCP COVER ASSY32P



TE Part #9-2208656-9  
58POS,MCON 1.2 CB,REC HSG,ASSY



TE Part #1587987-9  
RECEPTACLE ASSEMBLY, 250A, MSD



TE Part #1-1587987-7  
RECEPTACLE ASSEMBLY, Shunt, MSD



TE Part #1-2103172-7  
Plug Assembly, Shunt, MSD

Documents

Product Drawings

MQS RETAINER FOR 2POS REC.HSG

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1534112-1\_B.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1534112-1\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1534112-1\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

1534112-1

2 Position, Black, Retainer, PBT GF10, -40 – 120 °C [-40 – 248 °F]



Product Specifications

Product Specification

English