



Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers > LEAVYSEAL Connector Backshells



Number of Positions: 21

Primary Product Color: Black

Protection & Strain Relief Accessory Type: Cover - Cable Exit

Primary Product Material: PA

Cable Exit Angle: 90 °

[All LEAVYSEAL Connector Backshells \(25\)](#)

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
---	--------------------

Configuration Features

Number of Positions	21
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PA
Cable Exit Angle	90 °

Mechanical Attachment

Strain Relief	With
---------------	------

Dimensions

Compatible Cable Bundle Diameter Range	18.6 mm[.732 in]
--	------------------

Usage Conditions

--	--



Compatible With Connector Style	Housing For Male Terminals
Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Box
Packaging Quantity	200

Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-L489-CH8172
LEAVYSEAL Connector Housings

Also in the Series | LEAVYSEAL

Automotive Connector Caps & Covers (27)

Automotive Housings(119)

Other Automotive Connector Accessories(17)

Customers Also Bought

TE Part #CAT-L489-B128
LEAVYSEAL Connector Backshells

TE Part #CAT-L489-CH8172
LEAVYSEAL Connector Housings

TE Part #2112166-3
SLIDE, FOR 21 POS.

TE Part #2-2413900-1
2POS DIA 4MM PIN HSG ASSY-PCB, COD A

Documents

Product Drawings
COVER,90, FOR 21 POS.

English

CAD Files
Customer View Model
ENG_CVM_CVM_2112167-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_2112167-1_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_2112167-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[LEAVYSEAL CONNECTORS](#)

English

[ICT Terminals and Connectors Catalogue](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

German