

Product data sheet

Specifications



Symmetra PX 200kW Scalable to 250kW with Right Mounted Maintenance Bypass and Distribution

SY200K250DR-PD

Overview

Presentation	A high-performance, 3-phase, modular, scalable, power protection solution with industry-leading efficiency, capacity, and performance for medium to large data centers and mission critical environments.
Lead time	Usually Ships within 6 Weeks

Main

Main Input Voltage	480 V 3 phases 400 V 3 phases
Other Input Voltage	415 V
Main Output Voltage	480 V 3 phases 400 V 3 phases
Other Output Voltage	415 V
Rated power in W	200000 W
Rated power in VA	200000 VA
Output connector type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1
Battery type	VRLA
Provided equipment	Assembly service Installation guide Network management card Start-up service User manual

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Number of battery filled slots	13
Number of battery free slots	18
Battery recharge time	3.5 h
Number of battery replacement quantity	6
Battery overload operation	10 minutes at 125% and 60 seconds at 150%
Battery charger power	19200 W rated
Battery design life	5...8 year(s)
Extended runtime	1

General

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Bypass voltage tolerance	+/- 10 % settable from +/- 4/6/8 and 10 %
Number of power module free slots	2
Number of power module filled slots	8
Redundant	Yes

Physical

Colour	Black
Height	199.1 cm
Width	310 cm
Depth	107 cm
Net weight	4090 kg
USB compatible	No

Input

Network frequency	40...70 Hz auto-sensing
Number of input connectors	1 hard wire 4-wire (3P + E) 1 hard wire 5-wire (3P + N + E)
Input voltage limits	340...460 V 400 V 408...552 V 480 V
Max short time withstand current	50 kA
Input harmonic distortion	Less than 5 % for full load
Input protection type	3-pole circuit breaker
Load power factor	0.5 leading to 0.5 lagging
Input Power Factor at Full Load	0.99

Output

Maximum configurable power in W	500000 W
Harmonic distortion	Less than 2 %
Output frequency	50 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised 60 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Output voltage tolerance	+/- 1% static and +/- 5% at 100% load step
Output harmonic distortion	< 2% for 0 to 100% linear load and < 6% for full non-linear load
Output overload operation	10 minutes at 125% and 30 seconds at 150%
Bypass type	Built-in maintenance bypass Built-in static bypass
Efficiency	96.5 % (in battery operation)
Maximum configurable power in VA	500000 VA
Transfer time	2 ms typical

Conformance

Product certifications	cUL listed EUROBAT UL listed
Standards	CSA C22.2 No 107.3-05 EN/IEC 62040-1-1 EN/IEC 62040-2 EN/IEC 62040-3 UL 1778 UL 60950-1

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...3333 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m
Acoustic level	54 dBA
Heat dissipation	24757 Btu/h
NEMA degree of protection	NEMA 1
IP degree of protection	IP20

Communications & Management

Free slots	1
Preinstalled device	Network management card 2 with environmental monitoring, out of band access and Modbus
control panel	Touch screen LCD user interface
Emergency power off	Optional

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	215 cm
Package 1 Width	127 cm
Package 1 Length	411 cm
Package 1 Weight	4489 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained](#) >

[How we assess product sustainability](#) >

Use Better

 Materials and Substances	
EU RoHS Directive	Compliant with Exemptions
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

 Energy efficiency	
Energy Efficiency Optimized	Energy efficient product

Use Again

 Repack and remanufacture	
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins