

26.5mm Medium Spot Frosted TIR (10108)




Part no.	10108
Drawing no.	60423
Family	26.5mm
Type	TIR
Diameter	26.5
Beam	Medium Spot
Finish	Frosted




LEDs & Performances

Select LED to view available holders

Manu.	Performance Data	Images	IES/STP
 Avago Jade White	Eff: 81.7 FWHM: 24 Cd/lm: 4		View
 Cree XLamp CSP XD16 Cool White	Eff: 84 FWHM: 23 Cd/lm: 3.8		View
	Eff: 83.5 FWHM: 26		View

[Cree XLamp MH-B White](#)

Cd/lm: 2.7



[Cree XLamp MK-R White](#)

Eff: 84
FWHM: 29
Cd/lm: 3.1




[View](#)



[Cree XLamp MX-6 White](#)

Eff: 79.9
FWHM: 25
Cd/lm: 3.6



[View](#)



[Cree XLamp XB-D White](#)

Eff: 82
FWHM: 19
Cd/lm: 5.7



[Cree XLamp XHP-50 Gen 2 White](#)

Eff: 82
FWHM: 29
Cd/lm: 2.4




[View](#)



[Cree XLamp XHP-50 White](#)

Eff: 83.7
FWHM: 27
Cd/lm: 2.53



[View](#)



[Cree XLamp XHP35 HI White](#)

Eff: 83.5
FWHM: 20
Cd/lm: 4.4



[View](#)



[Cree XLamp XHP35 White](#)

Eff: 82
FWHM: 23
Cd/lm: 3.4




[View](#)



[Cree XLamp XM-L White](#)

Eff: 78.4
FWHM: 23
Cd/lm: 4.2




[View](#)



[Cree XLamp XM-L2 White](#)

FWHM: 22
Cd/lm: 4.8



[View](#)



[Cree XLamp XP-C White](#)

Eff: 83.9
FWHM: 17
Cd/lm: 6.1




[View](#)



[Cree XLamp XP-E White](#)

Eff: 80.2
FWHM: 20
Cd/lm: 4.4




[View](#)




[Cree XLamp XP-E2 White](#)

FWHM: 17
Cd/lm: 5.2



[Cree XLamp XP-G White](#)

Eff: 78.9
FWHM: 21
Cd/lm: 4.6




[View](#)



[Cree XLamp XP-G2 White](#)

FWHM: 20
Cd/lm: 5.7




[View](#)



[Cree XLamp XP-G3 White](#)

Eff: 83
FWHM: 21
Cd/lm: 2.48




[View](#)



[Cree XLamp XP-L HI White](#)

Eff: 83.5
FWHM: 19
Cd/lm: 4.7




[View](#)



[Cree XLamp XP-L White](#)

Eff: 83.4
FWHM: 22
Cd/lm: 3.9




[View](#)



[Cree XLamp XP-L2 White](#)

Eff: 84
FWHM: 25
Cd/lm: 3.1




[View](#)

Eff: 84.5



[Cree XLamp XQ-A Blue](#)

FWHM: 21
Cd/lm: 4.3




[View](#)



[Cree XLamp XQ-A Green](#)

Eff: 84.5
FWHM: 21
Cd/lm: 4.4



[View](#)



[Cree XLamp XQ-A Red](#)

Eff: 84.5
FWHM: 21
Cd/lm: 4.4



[View](#)


Eff: 83
FWHM: 6



[View](#)





Cd/lm: 10.36



[Cree XLamp XQ-A White](#)



Eff: 84
FWHM: 22
Cd/lm: 4




[Cree XLamp XQ-E HI Blue](#)

[View](#)



Eff: 84
FWHM: 22
Cd/lm: 4





[Cree XLamp XQ-E HI Green](#)

[View](#)



Eff: 84
FWHM: 22
Cd/lm: 4.1




[Cree XLamp XQ-E HI Red](#)

[View](#)



[Cree XLamp XQ-E HI White](#)

Eff: 84
FWHM: 12
Cd/lm: 6.12



[View](#)



[Cree XLamp XR White](#)

Eff: 84.2
FWHM: 26
Cd/lm: 3.1

[View](#)



[Cree XLamp XR-C White](#)

Eff: 84.8
FWHM: 21
Cd/lm: 4.2

[View](#)



[Cree XLamp XR-E White](#)


Eff: 84.3
FWHM: 22
Cd/lm: 3.8

[View](#)



[Cree XLamp XT-E HE White](#)

Eff: 84.5
FWHM: 23
Cd/lm: 3.8



[View](#)



[Cree XLamp XTE White](#)

FWHM: 20
Cd/lm: 5.4



[View](#)



[Everlight Shuen White](#)

Eff: 83.2
FWHM: 21
Cd/lm: 4.4



[View](#)



[LEDEngin 3W White](#)

Eff: 77.7
FWHM: 26
Cd/lm: 3.3




[View](#)



[LEDEngin 5W White](#)

Eff: 77.8
FWHM: 24
Cd/lm: 3.5




[View](#)



[LG 3535LG White](#)

FWHM: 22
Cd/lm: 5




[View](#)



[Lite-On R38386AS - S R38 IR](#)

Eff: 85
FWHM: 23
Cd/lm: 4.2




[View](#)



[LUMILEDS LUXEON 3030 White](#)

Eff: 82
FWHM: 18
Cd/lm: 4.89




[View](#)



[LUMILEDS LUXEON 3535 HV White](#)

Eff: 83.4
FWHM: 17
Cd/lm: 5.06




[View](#)



[LUMILEDS LUXEON 3535 L White](#)

Eff: 83
FWHM: 18
Cd/lm: 4.89



[View](#)



[LUMILEDS LUXEON 3535L Blue](#)

Eff: 85
FWHM: 23
Cd/lm: 3.8



[View](#)



[LUMILEDS LUXEON 3535L Green](#)

Eff: 85.5
FWHM: 23
Cd/lm: 3.9



[View](#)



[LUMILEDS LUXEON 3535L Red](#)

Eff: 85
FWHM: 22
Cd/lm: 4.2




[View](#)



[LUMILEDS LUXEON 5050 White](#)

Eff: 85
FWHM: 27
Cd/lm: 3



[View](#)



[LUMILEDS LUXEON C Blue](#)

Eff: 80.5
FWHM: 22
Cd/lm: 3.8



[View](#)



[LUMILEDS LUXEON C Lime](#)

Eff: 81.5
FWHM: 22
Cd/lm: 3.9



[View](#)




[LUMILEDS LUXEON C Red](#)

Eff: 79.5
FWHM: 23
Cd/lm: 3.6




[View](#)



[LUMILEDS LUXEON C White](#)

Eff: 77.4
FWHM: 20
Cd/lm: 5




[View](#)



[LUMILEDS LUXEON CSP 05 White](#)

Eff: 81
FWHM: 16
Cd/lm: 4.94




[View](#)



[LUMILEDS LUXEON CSP 10 White](#)

Eff: 81
FWHM: 19
Cd/lm: 4.16




[View](#)

Eff: 85



[LUMILEDS LUXEON CZ](#)

FWHM: 22
Cd/lm: 4.4




[View](#)



[LUMILEDS LUXEON IR Compact 850nm](#)

Eff: 84
FWHM: 22
Cd/lm: 4.3




[View](#)



[LUMILEDS LUXEON IR Domed 60 Degree](#)

Eff: 82.5
FWHM: 23
Cd/lm: 3.8



[View](#)



[LUMILEDS LUXEON IR Domed 90 Degree](#)

Eff: 83.5
FWHM: 23
Cd/lm: 4.2




[View](#)



[LUMILEDS LUXEON M White](#)

FWHM: 31
Cd/lm: 2.7



[View](#)



[LUMILEDS LUXEON MX White](#)

Eff: 83.52
FWHM: 29
Cd/lm: 2.3



[View](#)



[LUMILEDS LUXEON MZ White](#)

Eff: 83.9
FWHM: 24
Cd/lm: 3.2




[View](#)



[LUMILEDS LUXEON Q White](#)

Eff: 81.6
FWHM: 19
Cd/lm: 4.5




[View](#)



[LUMILEDS LUXEON R White](#)

Eff: 78.6
FWHM: 21
Cd/lm: 4.9




[View](#)



[LUMILEDS LUXEON Rebel ES White](#)

Eff: 78.6
FWHM: 21
Cd/lm: 4.9




[View](#)



[LUMILEDS LUXEON Rebel White](#)

Eff: 80.4
FWHM: 20
Cd/lm: 4.5



[View](#)



[LUMILEDS LUXEON T White](#)

Eff: 78.6
FWHM: 21
Cd/lm: 4.9



[View](#)




Eff: 83
FWHM: 19
Cd/lm: 4.7




[View](#)

[LUMILEDS LUXEON TX White](#)



[LUMILEDS LUXEON V White](#)

Eff: 82.5
FWHM: 25
Cd/lm: 3.1




[View](#)



[LUMILEDS LUXEON V2 White](#)

Eff: 84.5
FWHM: 24
Cd/lm: 3.8




[View](#)



[LUMILEDS LUXEON Z ES White](#)

Eff: 83.4
FWHM: 16
Cd/lm: 5.63




[View](#)




LUMILEDS LUXEON Z RGBW

Eff: 77.4
FWHM: 24
Cd/lm: 3.8



LUMILEDS LUXEON Z White

Eff: 83
FWHM: 12
Cd/lm: 6.5




[View](#)



Nichia 219 White

FWHM: 20
Cd/lm: 5.8




[View](#)



Nichia 229A White

Eff: 83
FWHM: 25
Cd/lm: 3.2




[View](#)



[Nichia 757G White](#)

Eff: 85
FWHM: 23
Cd/lm: 3.8




[View](#)



[Nichia NCSW E17A White](#)

Eff: 84.5
FWHM: 22
Cd/lm: 4.2




[View](#)



[Nichia NF2W 385AR-V2 White](#)

Eff: 85
FWHM: 23
Cd/lm: 3.8



[View](#)



[Nichia NFMW 481AR White](#)

Eff: 76.5
FWHM: 27
Cd/lm: 2.5





[View](#)



[Nichia NFMW 484AR White](#)

Eff: 85
FWHM: 28
Cd/lm: 2.7




[View](#)



[Nichia NFMW 486AR White](#)

Eff: 85
FWHM: 28
Cd/lm: 2.9




[View](#)



[Nichia NFMW 488AR White](#)

Eff: 85
FWHM: 28
Cd/lm: 2.7




[View](#)



[Nichia NV4W 144AR White](#)

Eff: 80.5
FWHM: 28.0°
Cd/lm: 2.4




[View](#)



[Nichia NVSL 219B White](#)

Eff: 84
FWHM: 23
Cd/lm: 4




[View](#)



[Nichia NVSW 219C White](#)

Eff: 84
FWHM: 23
Cd/lm: 3.7




[View](#)



[Nichia NVSW 319A White](#)

Eff: 83.5
FWHM: 24
Cd/lm: 3.5




[View](#)



[Nichia NVSW E21A White](#)

Eff: 82
FWHM: 18
Cd/lm: 5.14



[View](#)



[Nichia Top Emitting NCSL 119-H3 White](#)

Eff: 80
FWHM: 21
Cd/lm: 4.9




[View](#)



[Nichia Top Emitting NFSW 036 White](#)

Eff: 81.1
FWHM: 23
Cd/lm: 3.6



[View](#)




Eff: 77.8
FWHM: 24
Cd/lm: 3.7



[View](#)

Nichia Top Emitting NS3W 183T White




OSRAM
Opto Semiconductors

Osram OS DURIS E 2835 White

Eff: 85
FWHM: 23
Cd/lm: 3.9



[View](#)




OSRAM
Opto Semiconductors

Osram OS DURIS E2 White

Eff: 83
FWHM: 12
Cd/lm: 5.98



[View](#)




OSRAM
Opto Semiconductors

Osram OS DURIS E3 White

Eff: 86.9
FWHM: 14
Cd/lm: 6



[View](#)





[Osram OS DURIS P10 White](#)

Eff: 83.9
FWHM: 27
Cd/lm: 2.5



[View](#)



[Osram OS DURIS P8 White](#)

Eff: 83.5
FWHM: 19
Cd/lm: 4.8



[View](#)



[Osram OS DURIS S10 White](#)

Eff: 84.5
FWHM: 31
Cd/lm: 2.2




[View](#)



[Osram OS DURIS S2 White](#)

Eff: 87.6
FWHM: 18
Cd/lm: 5.2




[View](#)



[Osram OS DURIS S5 Deep Blue](#)

Eff: 85
FWHM: 23
Cd/lm: 4




[View](#)



[Osram OS DURIS S5 Green](#)

Eff: 85
FWHM: 23
Cd/lm: 4




[View](#)



[Osram OS DURIS S5 Red](#)

Eff: 85
FWHM: 22
Cd/lm: 4.2



[View](#)






[Osram OS DURIS S5 White](#)

Eff: 83
FWHM: 18
Cd/lm: 4.84



[View](#)


		
OSRAM Opto Semiconductors Osram OS DURIS S8 Gen2 White	Eff: 88 FWHM: 25 Cd/lm: 3.22  	View
OSRAM Opto Semiconductors Osram OS DURIS S8 White	Eff: 87.8 FWHM: 26 Cd/lm: 3.08  	View
OSRAM Opto Semiconductors Osram OS Osconiq P3737 White	Eff: 83 FWHM: 25 Cd/lm: 3.4  	View
		Eff: 91.5



Opto Semiconductors

FWHM: 22
Cd/lm: 4.5

[Osram OS OSLON Black SFH 4725S IR](#)




[View](#)



Opto Semiconductors

Eff: 85
FWHM: 21 x 21
Cd/lm: 4.5

[Osram OS OSLON Pure CSP GW VJLPE1 White](#)



[View](#)



Opto Semiconductors

Eff: 84.5
FWHM: 23
Cd/lm: 4.1

[Osram OS OSLON Square Flat White](#)



[View](#)



Opto Semiconductors

Eff: 83.3
FWHM: 19
Cd/lm: 4.8

[Osram OS OSLON Square Gen 3 White](#)



[View](#)



[Osram OS OSLON Square White](#)

Eff: 3
FWHM: 19
Cd/lm: 4.78



[View](#)



[Osram OS OSLON SSL 80 degree White](#)

Eff: 83.5
FWHM: 21
Cd/lm: 4.7



[View](#)



[Plessey PLW 7070GA White](#)

Eff: 83
FWHM: 30
Cd/lm: 2.3



[View](#)



[Samsung 3535 LH351A White](#)

FWHM: 21
Cd/lm: 5.2




[View](#)



[Samsung 3535 LH351B White](#)

Eff: 83
FWHM: 20
Cd/lm: 4.4




[View](#)



[Samsung 3535 LH351D White](#)

Eff: 84
FWHM: 25
Cd/lm: 3.4



[View](#)



[Samsung 3535 LH351Z White](#)

Eff: 83.4
FWHM: 19
Cd/lm: 4.89



[View](#)




Eff: 85
FWHM: 23



[View](#)

[Samsung CSP LH181B White](#)

Cd/lm: 3.9




[Samsung CSP LH231B White](#)

Eff: 85
FWHM: 24
Cd/lm: 3.7



[View](#)




[Samsung CSP LM101B White](#)

Eff: 85
FWHM: 22
Cd/lm: 4.2



[View](#)



[Samsung WH5 White](#)

Eff: 83.5
FWHM: 26
Cd/lm: 3.4




[View](#)





[Seoul CSP SZ8Y22 White](#)

Eff: 85.5
FWHM: 24
Cd/lm: 3.8




[View](#)



[Seoul CSP SZ8Y22P White](#)

Eff: 85
FWHM: 24
Cd/lm: 3.6




[View](#)



[Seoul CSP SZ8Y50 White](#)

Eff: 85
FWHM: 30
Cd/lm: 2.4



[View](#)




Eff: 83.5
FWHM: 18



[View](#)


[Seoul MidPower MJT3030 White](#)

Cd/lm: 4.7



[Seoul MidPower MJT4040 White](#)

Eff: 84
FWHM: 22
Cd/lm: 3.8



[View](#)



[Seoul MJT 5050 White](#)

Eff: 83.4
FWHM: 23
Cd/lm: 3.55



[View](#)



[Seoul P4 White](#)

Eff: 83.7
FWHM: 22
Cd/lm: 4.2



[View](#)



[Seoul P4 White](#)

Eff: 82.27
FWHM: 21
Cd/lm: 4.04




[View](#)



[Seoul SZ8Y11 White](#)

Eff: 84
FWHM: 22
Cd/lm: 4.1




[View](#)



[Seoul SZ8Y15 White](#)

Eff: 85
FWHM: 22
Cd/lm: 4.3




[View](#)



[Seoul SZ8Y19 White](#)

Eff: 83.7
FWHM: 20
Cd/lm: 4.21




[View](#)



[Seoul Z - Power Z5M White](#)

FWHM: 21
Cd/lm: 5




[View](#)



[SSC Z - Power Z1 White](#)

Eff: 81
FWHM: 26
Cd/lm: 3.2




[View](#)



[SSC Z - Power Z5 White](#)

Eff: 84.9
FWHM: 19
Cd/lm: 5.3




[View](#)



[SSC Z - Power Z5P White](#)

FWHM: 20
Cd/lm: 5.2




[View](#)

STANLEY

[Stanley 1N White](#)

FWHM: 24
Cd/lm: 3.9



[View](#)

STANLEY

[Stanley 6J White](#)

FWHM: 25
Cd/lm: 3.7




[View](#)

STANLEY

[Stanley 6J White](#)

Eff: 83
FWHM: 25
Cd/lm: 3.02



[View](#)


TOSHIBA

Eff: 83
FWHM: 19
Cd/lm: 4.55



[View](#)


[Toshiba TL 1L2 White](#)



TOSHIBA

[Toshiba TL 1L4 White](#)

Eff: 83
FWHM: 20
Cd/lm: 4.5



[View](#)