SMD CMOS PROGRAMMABLE CRYSTAL OSCILLATOR



2.5 x 2.0 x 0.81mm

AP2S

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive -MSL = N/A: Not Applicable

Pb RoHS Compliant

FEATURES:

- Performance comparable to fixed frequency oscillator
- Low RMS phase jitter
- Short lead time
- Suitable for mass production

ELECTRICAL SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range	V_{dd} = 3.3V	1		200	MHz	
	V_{dd} = 2.5V	1		200		
	V_{dd} = 1.8V	1		125		
Operating Temperature		-10		+60	°C	See options
Storage Temperature		-55		+125	°C	
Overall Frequency Stability*		-100		+100	ppm	See options
Supply Voltage (Vdd)	V_{dd} = 3.3V	3.125	3.30	3.465	V	Standard
	V_{dd} = 2.5V	2.375	2.50	2.625		Vdd option 1
	V_{dd} = 1.8V	1.71	1.80	1.89		Vdd option 2
Input Current	V_{dd} = 3.3V			35	mA	
	V_{dd} = 2.5V			30		
	V_{dd} = 1.8V			20		
Symmetry***		45	50	55	%	@ 1/2Vdd
Rise and Fall Time (Tr/Tf)**	V_{dd} = 3.3V			2	ns	
	V_{dd} = 2.5V			3		
	V_{dd} = 1.8V			4		
Output Load:				15	pF	CMOS

ABRACON

5101 Hidden Creek Lane Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sale please visit:
www.abracon.com

REVISED: 10.26.2021

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.

SMD CMOS PROGRAMMABLE CRYSTAL OSCILLATOR

AP2S

RoHS Compliant




2.5 x 2.0 x 0.81mm

ELECTRICAL SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Output Voltage	V_{OL}			0.33	V	V_{dd} = 3.3V
	V_{OH}	2.97				
	V_{OL}			0.25		V_{dd} = 2.5V
	V_{OH}	2.25				
	V_{OL}			0.18		V_{dd} = 1.8V
	V_{OH}	1.62				
Start-up Time				8	ms	
Tri-state function		"1" (VIH > 0.7*Vdd) or Open: Oscillation "0" (VIH < 0.3*Vdd): No Oscillation (High Impedance)				
Standby current (Power Down option)				400	uA	V_{dd} = 1.8, 2.5, 3.3V
RMS Phase Jitter			1	2	ps	V_{dd} = 3.3V
			1.1	2	ps	V_{dd} = 2.5V
			1.5	2	ps	V_{dd} = 1.8V
Aging:		-3.0		+3.0	ppm	@+25°C First year

* Inclusive of calibration @25°C, operating temperature range, input voltage variation, load variation, and first year aging. For±20ppm, inclusive of calibration @25°C, operating temperature range, and load variation.
** Transition times are measured between 10% and 90% of Vdd with an output load of 15 pF.
*** Only 40/60% is available for certain frequencies. Please contact Abracon when ordering.

TEST CIRCUIT:



CL = 15pF (including probe capacitance)

ABRACON

5101 Hidden Creek Lane Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sale please visit:
www.abracon.com

REVISED: 10.26.2021

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.

SMD CMOS PROGRAMMABLE CRYSTAL OSCILLATOR

AP2S

RoHS Compliant



2.5 x 2.0 x 0.81mm


OPTIONS & PART IDENTIFICATION:

AP2S [ ] - [ ] MHz - [ ][ ][ ] - [ ]


Supply Voltage	Frequency in MHz	Operating Temp.	Overall Freq. Stability	Tri-state pin	Packaging
Blank: 3.3V(*)	Please specify the frequency in MHz. e.g. 14.31818MHz	Blank: -10°C ~ +60°C	Blank: ±100ppm	B: Power Down (**)	Blank: Bulk
1: 2.5V		I: 0°C ~ +50°C	J: ±20ppm (***)		T: Tape & Reel (1k/reel)
2: 1.8V		E: -20°C ~ +70°C	R: ±25ppm		T3: Tape & Reel (3k/reel)
		F: -30°C ~ +70°C	K: ±30ppm		
		N: -30°C ~ +85°C	C: ±50ppm		
		L: -40°C ~ +85°C			

* 3.3V is standard
** PDB: Tri-state the output buffer and shut off the oscillator, <400µA when PDB enabled.
*** Contact ABRACON for availability

OUTLINE DRAWING:



UNIT: mm



Note 2
Recommend using an approximately 0.01uF bypass capacitor between Pin 2 and 4.

Pin	Function
1	Tri-State
2	GND/Case
3	Output
4	V_{dd}

Note 1
- Do not leave Pin 1 (Tri-State) floating
- If Pin 1 (Tri-State) is not utilized for toggling, it must be tied to V_{dd} (logic 1)

Dimensions: inches (mm)


ABRACON

5101 Hidden Creek Lane Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sale please visit:
www.abracon.com

REVISED: 10.26.2021

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.



RoHS Compliant

REFLOW PROFILE:

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process Classification Temperatures (T_c)		
Package Thickness	Volume mm³ <350	Volume mm³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2

Pb-Free Process Classification Temperatures (T_c)			
Package Thickness	Volume mm³ <350	Volume mm³ 350-2000	Volume mm³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	200°C
Time (T_{smin} to T_{smax}) (t_s)	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (T_{smax} to T_P)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	217°C
Time at liquidous (t_L)	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (T_P)*	**see Table 1**	**see Table 2**
Time (t_p)** within 5°C of the specified classification temperature (T_C)	20 sec.	30 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_P) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as supplier minimum and a user maximum.

ABRACON

5101 Hidden Creek Lane Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sale please visit:
www.abracon.com


REVISED: 10.26.2021

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.

TAPE & REEL:

T= Tape and reel (1,000pcs/reel)
T3= Tape and reel (3,000pcs/reel)



Dimensions: mm

ABRACON

5101 Hidden Creek Lane Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sale please visit:
www.abracon.com

REVISED: 10.26.2021

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.