

Features

- Ideally Suited for Automated Assembly Processes
- Halogen Free. "Green" Device (Note 1)
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)
- AEC-Q101 Qualified


Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance(Note2) : 833°C/W Junction to Ambient

Parameter	Symbol	Rating	Conditions
Power Dissipation	P_D	150mW	
Maximum Forward Voltage	V_F	0.9V	$I_F=10mA$


Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. Part mounted on FR-4 board with recommended pad layout.

Internal Structure and Marking Code




150 mW
Zener Diode
2.4 to 47 Volts

DFN1006-2L



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.037	0.041	0.95	1.05	
B	0.022	0.026	0.55	0.65	
C	0.016	0.020	0.40	0.50	
C1	-----	0.002	-----	0.05	
D	0.001	0.003	0.02	0.08	
E	0.026BSC		0.65BSC		
F	0.008	0.012	0.20	0.30	
G	0.018	0.022	0.45	0.55	

Suggested Solder Pad Layout



Electrical Characteristics @ 25°C Unless Otherwise Specified

MCC Part Number	Zener Voltage ⁽³⁾				Maximum Zener Impedance ⁽⁴⁾			Maximum Reverse Current $I_R @ V_R$		Typical Temperature Coefficient @ I_{ZTC}		Test Current	Marking Code
	$V_Z @ I_{ZT}$			I_{ZT} mA	$Z_{ZT} @ I_{ZT}$ Ω	$Z_{ZK} @ I_{ZK}$ mA	I_R μA	V_R V	mV/°C		I_{ZTC} mA		
	Min.(V)	Nom(V)	Max.(V)						Min	Max.			
BZT52C2V4L3PHE3	2.2	2.4	2.6	5	100	600	1.0	50	1.0	-3.5	0	5	WX
BZT52C2V7L3PHE3	2.5	2.7	2.9	5	100	600	1.0	20	1.0	-3.5	0	5	W1
BZT52C3V0L3PHE3	2.8	3.0	3.2	5	95	600	1.0	10	1.0	-3.5	0	5	W2
BZT52C3V3L3PHE3	3.1	3.3	3.5	5	95	600	1.0	5	1.0	-3.5	0	5	W3
BZT52C3V6L3PHE3	3.4	3.6	3.8	5	90	600	1.0	5	1.0	-3.5	0	5	W4
BZT52C3V9L3PHE3	3.7	3.9	4.1	5	90	600	1.0	3	1.0	-3.5	0	5	W5
BZT52C4V3L3PHE3	4.0	4.3	4.6	5	90	600	1.0	3	1.0	-3.5	0	5	W6
BZT52C4V7L3PHE3	4.4	4.7	5.0	5	80	500	1.0	3	2.0	-3.5	0.2	5	W7
BZT52C5V1L3PHE3	4.8	5.1	5.4	5	60	480	1.0	2	2.0	-2.7	1.2	5	9Y
BZT52C5V6L3PHE3	5.2	5.6	6.0	5	40	400	1.0	1	2.0	-2.0	2.5	5	9A
BZT52C6V2L3PHE3	5.8	6.2	6.6	5	10	150	1.0	3	4.0	0.4	3.7	5	9B
BZT52C6V8L3PHE3	6.4	6.8	7.2	5	15	80	1.0	2	4.0	1.2	4.5	5	9C
BZT52C7V5L3PHE3	7.0	7.5	7.9	5	15	80	1.0	1	5.0	2.5	5.3	5	9D
BZT52C8V2L3PHE3	7.7	8.2	8.7	5	15	80	1.0	0.7	5.0	3.2	6.2	5	9E
BZT52C9V1L3PHE3	8.5	9.1	9.6	5	15	100	1.0	0.5	6.0	3.8	7.0	5	9F
BZT52C10L3PHE3	9.4	10	10.6	5	20	150	1.0	0.2	7.0	4.5	8.0	5	9G
BZT52C11L3PHE3	10.4	11	11.6	5	20	150	1.0	0.1	8.0	5.4	9.0	5	9H
BZT52C12L3PHE3	11.4	12	12.7	5	25	150	1.0	0.1	8.0	6.0	10.0	5	9J
BZT52C13L3PHE3	12.4	13	14.1	5	30	170	1.0	0.1	8.0	7.0	11.0	5	9K
BZT52C15L3PHE3	13.8	15	15.6	5	30	200	1.0	0.1	10.5	9.2	13.0	5	9L
BZT52C16L3PHE3	15.3	16	17.1	5	40	200	1.0	0.1	11.2	10.4	14.0	5	9M
BZT52C18L3PHE3	16.8	18	19.1	5	45	225	1.0	0.1	12.6	12.4	16.0	5	9N
BZT52C20L3PHE3	18.8	20	21.2	5	55	225	1.0	0.1	14.0	14.4	18.0	5	9P
BZT52C22L3PHE3	20.8	22	23.3	5	55	250	1.0	0.1	15.4	16.4	20.0	5	9R
BZT52C24L3PHE3	22.8	24	25.6	5	70	250	1.0	0.1	16.8	18.4	22.0	5	9S
BZT52C27L3PHE3	25.1	27	28.9	2	80	300	0.5	0.1	18.9	21.4	25.3	2	9T
BZT52C30L3PHE3	28	30	32	2	80	300	0.5	0.1	21.0	24.4	29.4	2	9U
BZT52C33L3PHE3	31	33	35	2	80	325	0.5	0.1	23.1	27.4	33.4	2	9V
BZT52C36L3PHE3	34	36	38	2	90	350	0.5	0.1	25.2	30.4	37.4	2	9W
BZT52C39L3PHE3	37	39	41	2	130	350	0.5	0.1	27.3	33.4	41.2	2	9X
BZT52C43L3PHE3	40	43	46	2	100	700	0.5	0.1	32	37.6	50.6	2	9Q
BZT52C47L3PHE3	44	47	50	2	100	750	0.5	0.1	35	42.0	55.8	2	9Z

Note: 3. Short Duration Pulse Test Used to Minimize Self-heating Effect.
4. f=1KHz

Curve Characteristics

Fig. 1 - Typical Zener Breakdown Characteristics




Fig. 2 - Typical Zener Breakdown Characteristics




Fig. 3 - Typical Zener Breakdown Characteristics




Fig. 4 - Typical Zener Breakdown Characteristics




Fig. 5 - Typical Forward Characteristics





Fig. 6 - Power Derating Curve



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:10Kpcs/Reel

*****IMPORTANT NOTICE*****

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

*****LIFE SUPPORT*****

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

*****CUSTOMER AWARENESS*****

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.