









0955 266 6822 333	2	4-40 UNC	Black insulator	Samples
0955 266 3822 741	1	4-40 UNC	Black insulator	Reel Packaging (140 connectors)
0955 266 6822 741	2			
0955 266 7822 741	3			
0955 266 3821 741	1	M3		
0955 266 6821 741	2			
0955 266 7821 741	3			
Part number	PL	Thread		

Max. Temperature: 260°C during 10 seconds
Find further technical information on DS 09550200301

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.	
		All rights reserved		Created by ZHUANGJ		Inspected by LUOK		Standardisation HOFFMANN	
Department EL PD		Title D-Sub angled STD 15-pole male with screwlock		Date 2018-11-16		State Final Release		Doc-Key / ECM-Nr. 100682988/UGD/000/B 500000141375	
HARTING Electronics GmbH D-32339 Espelkamp		Type TB		Number 0955266X82X		Rev. B		Page 1/1	