










REV.	DATE	ECR NO.	DESCRIPTION
NC	03/20/05	—	INITIAL RELEASE
A	01/20/09	100073	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED
MOUNTING HOLE



8	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex TNC BULKHEAD CRIMP JACK (FOR RG–174/U, 316/U DOUBLE BRAID)				
7	SLEEVE	DELRI	NATURAL	1		DRAWN GRS		01/20/09						
6	HEX NUT	BRASS	NICKEL	1		CHECKED								
5	LOCK WASHER	BRASS	NICKEL	1		ISSUED				PART DESCRIPTION				
4	GASKET	SILICONE	RED	1		SHEET 1 OF 1				PART NO. 122358				
3	CONTACT PIN	BER. COPPER	GOLD	1		CAD FILE		C:/122/122358.DWG						
2	INSULATOR	DELRI	NATURAL	1						DWG. NO. 122358.DWG				
1	BODY	BRASS	NICKEL	1						REV. NC		SIZE A	SCALE NA	
DESCRIPTION		MATERIAL	FINISH	QTY										

Amphenol Connex

TNC BULKHEAD CRIMP JACK
(FOR RG-174/U, 316/U DOUBLE BRAID)

122358

122358.DWG

REV. NC

SIZE A

SCALE NA