





4		3		2		1																																																																																							
				used for: D-SUB HD																																																																																									
				<table><tr><th>Part NO.</th><th>POS.</th><th>A -0.76</th><th>B -0.25</th><th>C</th></tr><tr><td>164A17009X</td><td>15</td><td>31.19</td><td>16.46</td><td>25.00 ^{+0.12}/_{-0.13}</td></tr><tr><td>164A17019X</td><td>26</td><td>39.52</td><td>24.79</td><td>33.30 ^{+0.15}/_{-0.1}</td></tr><tr><td>164A17029X</td><td>44</td><td>53.42</td><td>38.50</td><td>47.04 ±0.13</td></tr><tr><td>164A17039X</td><td>62</td><td>69.70</td><td>54.96</td><td>63.50 ±0.13</td></tr></table>				Part NO.	POS.	A -0.76	B -0.25	C	164A17009X	15	31.19	16.46	25.00 ^{+0.12} / _{-0.13}	164A17019X	26	39.52	24.79	33.30 ^{+0.15} / _{-0.1}	164A17029X	44	53.42	38.50	47.04 ±0.13	164A17039X	62	69.70	54.96	63.50 ±0.13																																																													
Part NO.	POS.	A -0.76	B -0.25	C																																																																																									
164A17009X	15	31.19	16.46	25.00 ^{+0.12} / _{-0.13}																																																																																									
164A17019X	26	39.52	24.79	33.30 ^{+0.15} / _{-0.1}																																																																																									
164A17029X	44	53.42	38.50	47.04 ±0.13																																																																																									
164A17039X	62	69.70	54.96	63.50 ±0.13																																																																																									
																																																																																													
																																																																																													
Directive 2002/95/EC RoHS compliant																																																																																													
<table><tr><td colspan="4">APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL</td></tr><tr><td colspan="4">CUSTOMER APPROVAL DATE:</td></tr><tr><td colspan="2">NAME:</td><td colspan="2">TITLE:</td></tr><tr><td colspan="4">COMPANY NAME:</td></tr><tr><td colspan="4">APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL</td></tr></table>				APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL				CUSTOMER APPROVAL DATE:				NAME:		TITLE:		COMPANY NAME:				APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL				NOTES: 1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin Nickel 2. INSULATORS: PBT GF UL 94 V-0, BLACK 3. CONTACTS: COPPER ALLOY PLATING: GOLD FLASH over NICKEL SOLDER CUP ACCEPTS CABLE AWG 22 4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC																																																																					
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL																																																																																													
CUSTOMER APPROVAL DATE:																																																																																													
NAME:		TITLE:																																																																																											
COMPANY NAME:																																																																																													
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL																																																																																													
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				<table><tr><td colspan="4">CONEC CORPORATION</td><td colspan="2">tolerance</td><td colspan="2"> dim. in mm</td><td colspan="2">scale: 2:1</td></tr><tr><td colspan="4">BRAMPTON, ONTARIO</td><td colspan="2"></td><td colspan="2"></td><td colspan="2">material: SEE NOTES</td></tr><tr><td></td><td></td><td></td><td></td><td>2001</td><td>date</td><td colspan="2">name</td><td colspan="2" rowspan="5">title: D-SUB HD FEMALE 15-62pos. SOLDER CUP</td></tr><tr><td></td><td></td><td></td><td></td><td>drawn</td><td>04.10.</td><td colspan="2">Parei</td></tr><tr><td></td><td></td><td></td><td></td><td>appd.</td><td>04.10.</td><td colspan="2">E. Mickenbecker</td></tr><tr><td></td><td></td><td></td><td></td><td>norm</td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>d-old</td><td colspan="2"></td></tr><tr><td>2 x b</td><td>Ä 3104</td><td>04.09.08</td><td>Petker</td><td colspan="2" rowspan="3"></td><td colspan="2">dwg no: AutoCAD 2000</td><td colspan="2">DIN-A 4</td></tr><tr><td>a</td><td>Origin</td><td></td><td></td><td colspan="2">16K1A322A</td><td colspan="2">sh: 1/1</td></tr><tr><td>rev.</td><td>description</td><td>date</td><td>name</td><td colspan="2">part no: SEE TABLE</td><td colspan="2"></td></tr></table>				CONEC CORPORATION				tolerance		 dim. in mm		scale: 2:1		BRAMPTON, ONTARIO								material: SEE NOTES						2001	date	name		title: D-SUB HD FEMALE 15-62pos. SOLDER CUP						drawn	04.10.	Parei						appd.	04.10.	E. Mickenbecker						norm							d-old			2 x b	Ä 3104	04.09.08	Petker			dwg no: AutoCAD 2000		DIN-A 4		a	Origin			16K1A322A		sh: 1/1		rev.	description	date	name	part no: SEE TABLE			
CONEC CORPORATION				tolerance		 dim. in mm		scale: 2:1																																																																																					
BRAMPTON, ONTARIO								material: SEE NOTES																																																																																					
				2001	date	name		title: D-SUB HD FEMALE 15-62pos. SOLDER CUP																																																																																					
				drawn	04.10.	Parei																																																																																							
				appd.	04.10.	E. Mickenbecker																																																																																							
				norm																																																																																									
				d-old																																																																																									
2 x b	Ä 3104	04.09.08	Petker			dwg no: AutoCAD 2000		DIN-A 4																																																																																					
a	Origin					16K1A322A		sh: 1/1																																																																																					
rev.	description	date	name			part no: SEE TABLE																																																																																							
4		3		2		1																																																																																							