



Part Number : [1713151837](#)
Product Description : Impel 90 Ohm, 4 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Right Endwall, 8 Columns, 64 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.36mm
Series Number : 171315
Status : Active
Product Category : Backplane Connectors



Documents & Resources

Drawings

[1713151837_sd.pdf](#)
[PK-78888-084-001.pdf](#)

3D Models and Design Files

[1713151837_stp.zip](#)
[1713202061REVA-000.pdf](#)
[2040661117-000.pdf](#)
[1713202061-000.zip](#)
[2040661117-000.zip](#)
[SYM-171315-1837-001.zip](#)

Specifications

[1713209994-AS-000.pdf](#)
[AS-171320-990-001.pdf](#)
[AS-171320-991-001.pdf](#)
[AS-171320-992-001.pdf](#)
[PS-171320-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Backplane Connectors
Series	171315
Description	Impel 90 Ohm, 4 Pair Vertical Backplane Header, 1.90mm Pitch, Unguided, Right Endwall, 8 Columns, 64 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.36mm
Application	Backplane
Component Type	PCB Header
Product Name	Impel
UPC	887191343655

Agency

CSA	152514
UL	E29179

Electrical

Current - Maximum per Contact	0.75A
Data Rate	40.0 Gbps
Impedance	90Ω
Shield Type	Full Shield
Voltage - Maximum	29.9V AC (RMS)/DC

Physical

Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.976/g
Number of Columns	8
Number of Pairs	4
Number of Rows	8
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55° to +85°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Unguided, 8 Columns, 64 Circuits, Plated Through Hole Dimension 0.36mm	<u>1713201038</u>
---	-------------------

This document was generated on Apr 22, 2025