







NOTES:

1. MATERIAL: SEE TABLE.
2. FINISHES: SEE TABLE.
3. "XX" REFERS TO QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLAINT.
5. -59 OPTION: SCREWS SUPPLIED UNASSEMBLED.

4	XX	SCREW & WASHER, #8-32, PAN HEAD (-50 OPT)	BRASS	NICKEL PLATE
3	XX	SCREW, #8-32, BIN HEAD (A- OPT)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL, FT, 8-32, SN/B	BRASS	TIN PLATE
1	1	INSULATOR, SINGLE ROW	POLYESTER (PBT)	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

ADD -50-59 OPT
EC NO: IPG2014-1260
DRAWN: JENCINAS 2013/10/31
CHKD: JENCINAS
APPR: JMACNEIL 2014/03/10
DESCRIPTION
REV

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .01	± .001
2 PLACES	± .03	± .003
1 PLACE	± .06	± .006
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
JENCINAS	2013/08/27
CHECKED BY	DATE
JMACNEIL	2013/08/27
APPROVED BY	DATE
JMACNEIL	2014/03/10
MATERIAL NO.	
SIZE	B

SCALE 2:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
TITLE 11.11/.438" SR BTS, INSUL TURRET, FT ASSY, #8-32 SCREWS		
 MOLEX INCORPORATED		
DOCUMENT NO. SD-38732-002		SHEET NO. 1 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

10 9 8 7 6 5 4 3 2 38732

NO. OF CIRCUITS	DIM. "A"		DIM. "B"		DIM. "C"		DIM. "D"		ASSEMBLY MATERIAL NO. (-A OPT)	ASSEMBLY MATERIAL NO. (-A-50 OPT)	ASSEMBLY MATERIAL NO. (-A-50-59 OPT)
	mm	in	mm	in	mm	in	mm	in			
02	43.5	1.71	11.11	.438	33.34	1.313	24.5	.97	38732-2502	38732-2702	
03	54.6	2.15	22.23	.875	44.45	1.750	35.7	1.40	38732-2503	38732-2703	
04	65.7	2.59	33.34	1.313	55.56	2.188	46.8	1.84	38732-2504	38732-2704	38739-0616
05	76.8	3.03	44.45	1.750	66.68	2.625	57.9	2.28	38732-2505	38732-2705	
06	87.9	3.46	55.56	2.188	77.79	3.063	69.0	2.72	38732-2506	38732-2706	
07	99.1	3.90	66.68	2.625	88.90	3.500	80.1	3.15	38732-2507	38732-2707	
08	110.2	4.34	77.79	3.063	100.01	3.938	91.2	3.59	38732-2508	38732-2708	38739-0617
09	121.3	4.78	88.90	3.500	111.13	4.375	102.3	4.03	38732-2509	38732-2709	
10	132.4	5.21	100.01	3.938	122.24	4.813	113.4	4.47	38732-2510	38732-2710	38739-0618
11	143.5	5.65	111.13	4.375	133.35	5.250	124.6	4.90	38732-2511	38732-2711	
12	154.6	6.09	122.24	4.813	144.46	5.688	135.7	5.34	38732-2512	38732-2712	
13	165.7	6.53	133.35	5.250	155.58	6.125	146.8	5.78	38732-2513	38732-2713	
14	176.8	6.96	144.46	5.688	166.69	6.563	157.9	6.22	38732-2514	38732-2714	
15	188.0	7.40	155.58	6.125	177.80	7.000	169.0	6.65	38732-2515	38732-2715	
16	199.1	7.84	166.69	6.563	188.91	7.438	180.1	7.09	38732-2516	38732-2716	
17	210.2	8.28	177.80	7.000	200.03	7.875	191.2	7.53	38732-2517	38732-2717	
18	221.3	8.71	188.91	7.438	211.14	8.313	202.3	7.97	38732-2518	38732-2718	
19	232.4	9.15	200.03	7.875	222.25	8.750	213.5	8.40	38732-2519	38732-2719	
20	243.5	9.59	211.14	8.313	233.36	9.188	224.6	8.84	38732-2520	38732-2720	
21	254.6	10.03	222.25	8.750	244.48	9.625	235.7	9.28	38732-2521	38732-2721	
22	265.7	10.46	233.36	9.188	255.59	10.063	246.8	9.72	38732-2522	38732-2722	
23	276.9	10.90	244.48	9.625	266.70	10.500	257.9	10.15	38732-2523	38732-2723	
24	288.0	11.34	255.59	10.063	277.81	10.938	269.0	10.59	38732-2524	38732-2724	
25	299.1	11.78	266.70	10.500	288.93	11.375	280.1	11.03	38732-2525	38732-2725	
26	310.2	12.21	277.81	10.938	300.04	11.813	291.2	11.47	38732-2526	38732-2726	
27	321.3	12.65	288.93	11.375	311.15	12.250	302.4	11.90	38732-2527	38732-2727	
28	332.4	13.09	300.04	11.813	322.26	12.688	313.5	12.34	38732-2528	38732-2728	
29	343.5	13.53	311.15	12.250	333.38	13.125	324.6	12.78	38732-2529	38732-2729	
30	354.6	13.96	322.26	12.688	344.49	13.563	335.7	13.22	38732-2530	38732-2730	

(B)
(B)
(B)

SEE SHEET ONE EC NO: IPG2014-1260 DRAWN: JENCINAS 2013/11/19 CHKD: JMACNEIL APPR: JMACNEIL 2014/03/10 REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY JENCINAS	DATE 2013/08/27	TITLE 11.11/.438" SR BTS, INSUL TURRET, FT ASSY, #8-32 SCREWS	
		4 PLACES	± .---	± .---	CHECKED BY JMACNEIL	DATE 2013/08/27		MOLEX INCORPORATED
		3 PLACES	± .---	± .005	APPROVED BY JMACNEIL	DATE 2014/03/10	DOCUMENT NO. SD-38732-002	
		2 PLACES	± 0.13	± .01	MATERIAL NO.		SHEET NO. 2 OF 2	
		1 PLACE	± 0.3	± .---	SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
		ANGULAR ± 2 °						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						