**Part Number :** 190070028
**Product Description :** Flag InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm$^2$) Wire, Metal Strip, Tab 6.35 x 0.81mm
**Series Number :** 19007
**Status :** Active
**Product Category :** Quick Disconnects
**Engineering Part Number :** BB-2221Z



## Documents and Resources

### Drawings

190070028_sd.pdf

PK-19007-001-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-19902-008-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Quick Disconnects |
| Series | 19007 |
| Description | Flag InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm$^2$) Wire, Metal Strip, Tab 6.35 x 0.81mm |
| Product Name | InsulKrimp |
| Type | Flag Terminal |
| UPC | 800753031937 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E79133 |

### Electrical

| | |
|---|---|
| Voltage - Maximum | 600V |

### Physical

| | |
|---|---|
| Barrel Type | Closed |
| Color - Resin | Blue |
| Flammability | 94V-2 |

Downloaded from Arrow.com.

| | |
|---|---|
| Gender | Female |
| Glow-Wire Capable | Yes |
| Insulated | Fully |
| Insulation | Nylon (PA) |
| Lock to Mating Part | No |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 1.300/g |
| Orientation | Flag |
| Packaging Type | Reel |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | No |
| Tab Thickness | 0.81mm |
| Tab Width | 6.35mm |
| Temperature Range - Operating | -65° to +105°C |
| Wire Insulation Diameter | 5.08mm max. |
| Wire Size (AWG) | 14, 16 |
| Wire Size $mm^2$ | 1.30-2.00 |

**Solder Process Data**

| | |
|---|---|
| Lead-Free Process Capability | N/A |

## Application Tooling

## Global

| Description | Part Number |
|---|---|
| Mini-Mac Applicator Rear Feed | 638026400 |



Downloaded from Arrow.com.